

TECHSPEC[®] 12.7mm Dia. x 50.8mm FL, VIS 0°, Inked, Plano-Convex Lens



Stock #62-568-INK 3-5 DAYS

[Other Coating Options](#)



1



A\$80.80

ADD TO CART

Qty 1-9

A\$80.80

Qty 10+

A\$72.80

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
12.70 ±0.025

Effective Focal Length EFL (mm):
50.80 @ 587.6nm

Back Focal Length BFL (mm): 49.15
Coating: VS 0° (425-675nm)
Coating Specification: R _{avg} ≤0.4% @ 425 - 675nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 2.50 ±0.10
Edge Thickness ET (mm): 1.72
Radius R₁ (mm): 26.25
Clear Aperture CA (mm): 11.7
f/#: 4
Numerical Aperture NA: 0.13
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 425 - 675
Damage Threshold, By Design: ☐ 5 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View