

TECHSPEC® 12.7mm Dia. x 6.35mm FL, Uncoated, ZnSe Aspheric Lens

See More by [Coherent®](#)



TECHSPEC Zinc Selenide (ZnSe) Aspheric Lenses

Stock **#39-469** 3-5 DAYS

[Other Coating Options](#)

- 1 +

A\$1,280.00

ADD TO CART

Qty 1-10
A\$1,280.00
Qty 11+
A\$1,156.32
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
12.70 +0.00/-0.10

Effective Focal Length EFL (mm):
6.35

Numerical Aperture NA: 1.00
Back Focal Length BFL (mm): 4.69
Substrate:  Coherent® Infrared ZnSe
Asphere Figure Error, RMS @ 632.8nm: λ/2
Coating: Uncoated
Centering (arcmin): ≤20
Centering, ETD (μm): ≤50.8
Surface Quality: 40-20
Clear Aperture CA (mm): 11.43
Edge Thickness ET (mm): 1.89
Center Thickness CT (mm): 4.00 ±0.10
f/#: 0.5
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Wavelength Range (nm): 600 - 18000
Conjugate Distance: Infinite
Surface Roughness (Angstroms): <50 RMS
Power (P-V) @ 10.6μm: λ/10
Power (P-V) @ 632.8nm: λ/10

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View