

TECHSPEC[®] 12.7mm Diameter, NIR II Coated, Calcium Fluoride Window



TECHSPEC Calcium Fluoride (CaF₂) Windows

Stock #17-603 3-5 DAYS

-

1

+

A\$256.00

ADD TO CART

Qty 1-10

A\$256.00

Qty 11+

A\$230.40

Volume Pricing

[Request Quote](#)

Get Product Downloads



Abbe Number (v_d):
94.99

Axis Orientation:
Random

Bevel:
Protective as needed

Clear Aperture (%) : 90
Clear Aperture CA (mm) : 11.43
Diameter (mm) : 12.70 +0.0/-0.1
Thickness (mm) : 2.00 ±0.10
Coating : NIR II (750-1550nm)
Coating Specification : R _{abs} ≤1.5% @ 750 - 800nm R _{abs} ≤1.0% @ 800 - 1550nm R _{avg} ≤0.7% @ 750 - 1550nm
Coefficient of Thermal Expansion CTE (10⁻⁶/°C) : 18.85
Density (g/cm³) : 3.18
Edges : Fine Ground
Index of Refraction n_d : 1.434
Knoop Hardness (kg/mm²) : 158.3
Parallelism (arcmin) : <1
Poisson's Ratio : 0.26
Substrate : Calcium Fluoride (CaF ₂) Vacuum UV Grade
Surface Flatness (P-V) : λ/2
Surface Quality : 40-20
Type : Protective Window
Wavelength Range (nm) : 750 - 1550
Young's Modulus (GPa) : 75.8
Damage Threshold, By Design : ☐ 8 J/cm² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015 : Compliant
Certificate of Conformance : View
Reach 235 : Compliant