

12.7mm, MgF₂ Coated, Penta Prism Beamsplitter



Stock **#66-632** **4 In Stock**

-

1

+

A\$408^{.00}

ADD TO CART

Volume Pricing	
Qty 1-5	A\$408.00 each
Qty 6-25	A\$326.40 each
Qty 26-49	A\$302.40 each
Need More?	Request Quote

Product Downloads

General	
Standard Beamsplitter	Type:
Physical & Mechanical Properties	
>90	Clear Aperture (%):
Prism	Construction:

Dimensional Tolerance (mm):	
±0.10	
Optical Properties	
Beam Deviation (°):	
90, 180	
Beam Deviation Tolerance (arcsec):	
±10	
Coating:	
MgF ₂ on Entrance and Exit Faces	
Polarization:	
Ts - Tp ≤ 15%	
Reflection/Transmission Ratio (R/T):	
50/50	
Reflection/Transmission Tolerance (%):	
±5	
Substrate: ☐	
N-BK7	
Surface Flatness (P-V):	
λ/4	
Surface Quality:	
40-20	
Wavelength Range (nm):	
450 - 650	

Regulatory Compliance	
RoHS 2015:	
Compliant	
Reach 209:	
Compliant	
Certificate of Conformance:	
View	


Product Details

- 50% Reflection / 50% Transmission
- Beam Deviation Insensitive to Alignment
- Designed for Visible Wavelengths

Penta Prism Beamsplitters are constructed by cementing a precision [penta prism](#) and a [wedge prism](#) together, and applying an appropriate interference coating to one of the traditionally reflective surfaces. Since slight movements of a penta prism do not affect the true right angle at which light rays are reflected, the deviation between the transmitted and reflected light rays is highly controllable and will not vary by more than 10arcsec.

Note: Outgoing beams are partially polarized.

Technical Information



Stock No.	A	B	C	D	E
#66-632	12.70mm	12.70mm	5.26mm	13.75mm	12.70mm
#66-633	20.00mm	20.00mm	8.28mm	21.65mm	20.00mm
#66-634	25.40mm	25.40mm	10.52mm	27.49mm	25.40mm

