

12.7mm Sq 70R/30T, UV-NIR Polka-Dot Beamsplitter



Stock #47-607 3-5 DAYS

-

1

+

A\$232.00

ADD TO CART

Qty 1-10
A\$232.00
Qty 11+
A\$197.20
Volume Pricing
Request Quote

Get Product Downloads



Angle of Incidence (°):
0 - 45

Center to Center Spacing (mm):
0.15

Clear Aperture (%):
90

Coating: Square Aluminum (AlMgF ₂) Apertures
Construction: Polka-Dot
Dimensional Tolerance (mm): +0.0/-0.5
Dimensions (mm): 12.7 x 12.7
Minimum Aperture (mm): 2.00
Operating Temperature (°C): 150 Maximum
Parallelism (arcmin): <3
Reflection/Transmission Ratio (R/T): 70/30
Reflection/Transmission Tolerance (%): ±5 @ 45°
Substrate:  Fused Silica (Corning 7980)
Surface Quality: 80-50
Thickness (mm): 1.65 ±0.1
Type: Standard Beamsplitter
Wavelength Range (nm): 250 - 2000

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View