

[See all 51 Products in Family](#)

TECHSPEC[®] 12.7mm Dia. x 20mm FL, Uncoated, ZnSe Plano-Convex Lens

See More by [Coherent®](#)



TECHSPEC Zinc Selenide (ZnSe) Plano-Convex (PCX) Lenses

Stock **#39-522** **7 In Stock**

[Other Coating Options](#)

-

1

+

A\$337⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-10	A\$337.60 each
Qty 11-25	A\$304.00 each
Qty 26-49	A\$238.40 each
Need More?	Request Quote

Product Downloads

General

Plano-Convex Lens

Type:

Physical & Mechanical Properties

12.70 +0.00/-0.10

Diameter (mm):

≤50.8	Centering, ETD (μm):
1.85 ±0.10	Center Thickness CT (mm):
1.12	Edge Thickness ET (mm):
11.43	Clear Aperture CA (mm):
Protective as needed	Bevel:

<50 RMS	Surface Roughness (□):
---------	------------------------

Optical Properties

20.00 @ 10.6μm	Effective Focal Length EFL (mm):
19.23	Back Focal Length BFL (mm):

Uncoated	Coating:
Coherent® Infrared ZnSe	Substrate: □

40-20	Surface Quality:
λ	Power (P-V) @ 632.8nm:

λ/20	Irregularity (P-V) @ 10.6μm:
28.05	Radius R ₁ (mm):

1.57	f/#:
0.32	Numerical Aperture NA:

600 - 18000	Wavelength Range (nm):
<0.0005 @ 10.6μm	Bulk Absorption Coefficient (cm ⁻¹):

Electrical

λ/10	Power (P-V) @ 10.6μm:
------	-----------------------

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 242:

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details


- Edmund Optics® Designed, Coherent® Manufactured
- Premier Grade ZnSe Material
- Uncoated or Broadband AR Coating Options

TECHSPEC® Zinc Selenide (ZnSe) Plano-Convex (PCX) Lenses are designed for focusing or collimation applications in the mid-wave and longwave infrared spectrum. Manufactured by Coherent®, these lenses feature Infrared ZnSe material with <0.0005cm⁻¹ bulk absorption at 10.6μm and are available uncoated or with a variety of broadband anti-reflection coating options. The 8-12μm coating is ideal for use with CO₂ lasers and thermal camera applications, whereas the dual band 3-12μm coating is ideal for hyperspectral applications. TECHSPEC® Zinc Selenide PCX Lenses feature an irregularity of <λ/20 at 10.6μm, 40-20 surface quality, and <50Å surface roughness. Three diameter options are available, with effective focal lengths ranging from 12.7mm to 250mm.

Notes: II-VI Incorporated is now Coherent Corp.

Special care should be taken when handling Zinc Selenide as it is a toxic material. Always wear rubber or plastic gloves to avoid risk of contamination.

Technical Information



AR COATED ZINC SELENIDE																													
ZnSe with 3-12μm AR Coating Typical Transmission <table border="1"><thead><tr><th>λ (μm)</th><th>T (%)</th></tr></thead><tbody><tr><td>2</td><td>70</td></tr><tr><td>3</td><td>95</td></tr><tr><td>4</td><td>97</td></tr><tr><td>5</td><td>95</td></tr><tr><td>6</td><td>97</td></tr><tr><td>7</td><td>96</td></tr><tr><td>8</td><td>95</td></tr><tr><td>9</td><td>96</td></tr><tr><td>10</td><td>96</td></tr><tr><td>11</td><td>96</td></tr><tr><td>12</td><td>94</td></tr><tr><td>13</td><td>90</td></tr><tr><td>14</td><td>86</td></tr></tbody></table> Typical transmission of a ZnSe window with BBAR (3000-12000nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{avg} < 5.0\%$ @ 3 - 12μm Data outside this range is not guaranteed and is for reference only. Click Here to Download Data	λ (μm)	T (%)	2	70	3	95	4	97	5	95	6	97	7	96	8	95	9	96	10	96	11	96	12	94	13	90	14	86	
λ (μm)	T (%)																												
2	70																												
3	95																												
4	97																												
5	95																												
6	97																												
7	96																												
8	95																												
9	96																												
10	96																												
11	96																												
12	94																												
13	90																												
14	86																												
ZnSe with 8-12μm AR Coating Typical Transmission <table border="1"><thead><tr><th>λ (μm)</th><th>T (%)</th></tr></thead><tbody><tr><td>6</td><td>70</td></tr><tr><td>7</td><td>90</td></tr><tr><td>8</td><td>100</td></tr><tr><td>9</td><td>100</td></tr><tr><td>10</td><td>100</td></tr><tr><td>11</td><td>99</td></tr><tr><td>12</td><td>96</td></tr><tr><td>13</td><td>92</td></tr><tr><td>14</td><td>86</td></tr></tbody></table> Typical transmission of a ZnSe window with BBAR (8000-12000nm) coating at 0° AOI. The blue shaded region indicates the coating design wavelength range, with the following specification: $R_{avg} \leq 0.5\%$ @ 8 - 12μm Data outside this range is not guaranteed and is for reference only. Click Here to Download Data	λ (μm)	T (%)	6	70	7	90	8	100	9	100	10	100	11	99	12	96	13	92	14	86									
λ (μm)	T (%)																												
6	70																												
7	90																												
8	100																												
9	100																												
10	100																												
11	99																												
12	96																												
13	92																												
14	86																												

Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools

Compatible Mounts

;