

[See all 4 Products in Family](#)

# 12.7mm Dia. x 25.4mm FL, Uncoated, ISP Optics Calcium Fluoride (CaF<sub>2</sub>) DCX Lens | CF-BX-12-25

See More by [ISP Optics](#)



Calcium Fluoride Double-Convex (DCX) Lenses

Stock **#24-763** CLEARANCE **1 In Stock**

-

1

+

A\$233<sup>.60</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-9        | A\$233.60 each                |
| Qty 10+        | A\$211.20 each                |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

| General            |               |
|--------------------|---------------|
| Double-Convex Lens | Type:         |
| CF-BX-12-25        | Model Number: |

Physical & Mechanical Properties

|                      |                           |
|----------------------|---------------------------|
| 12.70 +0.00/-0.13    | Diameter (mm):            |
| <3                   | Centering (arcmin):       |
| Protective as needed | Bevel:                    |
| 3.60 ±0.20           | Center Thickness CT (mm): |
| 1.50                 | Edge Thickness ET (mm):   |
| 11.43                | Clear Aperture CA (mm):   |

|                                      |                                     |
|--------------------------------------|-------------------------------------|
| Optical Properties                   |                                     |
| 25.40 @ 5µm                          | Effective Focal Length EFL (mm):    |
| Uncoated                             | Coating:                            |
| Calcium Fluoride (CaF <sub>2</sub> ) | Substrate: <input type="checkbox"/> |
| 60-40                                | Surface Quality:                    |
| λ                                    | Irregularity (P-V) @ 632.8nm:       |
| 19.77                                | Radius R <sub>1</sub> (mm):         |
| 19.77                                | Radius R <sub>2</sub> (mm):         |
| 2.00                                 | f/#:                                |
| ±2                                   | Focal Length Tolerance (%):         |
| 0.25                                 | Numerical Aperture NA:              |
| 300 - 8000                           | Wavelength Range (nm):              |


|                       |                             |
|-----------------------|-----------------------------|
| Regulatory Compliance |                             |
| Compliant             | RoHS 2015:                  |
| View                  | Certificate of Conformance: |
| Compliant             | Reach 240:                  |



## Product Details

- Greater than 90% Transmission from 350nm-7µm
- Low Index of Refraction
- High Laser Damage Threshold

ISP Optics Calcium Fluoride Double-Convex (DCX) Lenses are ideal for finite imaging applications requiring high transmission in the infrared wavelength spectrum. Calcium Fluoride features greater than 90% transmission from 350nm to 7µm and a low refractive index, allowing it to be used without an antireflective coating. In addition, its low absorption and high damage threshold makes it a popular choice for use with excimer lasers. ISP Optics Calcium Fluoride Double-Convex (DCX) Lenses offer low solubility and superior hardness compared to other fluoride-based substrates, allowing for use in harsh environments.

## Technical Information





## Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools