

TECHSPEC[®] 12.7mm Dia x 31.8mm FL, MgF₂ Coated, Achromatic Doublet Lens



MgF₂ Coated Achromatic Lenses



Stock **#49-761** 3-5 DAYS

[Other Coating Options](#)

-

1

+

A\$121.60

ADD TO CART

Qty 1-5

A\$121.60

Qty 6+

A\$97.20

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
12.70 +0.0/-0.025

Effective Focal Length EFL (mm):

31.75
Focal Length Tolerance (%): ±1
Back Focal Length BFL (mm): 28.83
Focal Length Specification Wavelength (nm): 587.6
Clear Aperture CA (mm): 11.70
Centering (arcmin): <1
Center Thickness CT (mm): 5.75 ±0.20
Center Thickness CT 1 (mm): 4.00 ±0.10
Center Thickness CT 2 (mm): 1.75 ±0.10
Radius R ₁ (mm): 21.13
Radius R ₂ (mm): -16.69
Radius R ₃ (mm): -61.73
Edge Thickness ET (mm): 4.45
Substrate:  N-SSK8 / N-SF56
Surface Quality: 40-20
f/#: 2.5
Numerical Aperture NA: 0.20
Coating: MgF ₂ (400-700nm)
Coating Specification: R _{avg} ≤1.75% @400 - 700nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Achromatic Lens
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View