

[See all 22 Products in Family](#)

## 12mm Dia. x 12mm FL Protected Gold, Concave Mirror



Stock #43-833 **3 In Stock**

A\$98<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-49	<b>A\$98.40</b> each
Qty 50-99	<b>A\$84.80</b> each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Spherical Mirror **Type:**

### Physical & Mechanical Properties

$\pm 0.5$  **Thickness Tolerance (mm):**

12.00  $\pm 0.50$  **Diameter (mm):**

90 **Clear Aperture (%):**

3.0 Edge Thickness ET (mm):

## Optical Properties

Metal Coating Type:

Protected Gold (700-10000nm) Coating:

700 - 10000 Wavelength Range (nm):

12.00 Effective Focal Length EFL (mm):

N-BK7 Substrate: □

f/1 Aperture (f/#):

Coating Specification:  
R<sub>avg</sub> >96% @ 700 - 2000nm  
R<sub>avg</sub> >96% @ 2000 - 10,000nm

±2 Focal Length Tolerance (%):

24.00 Radius R<sub>1</sub> (mm):

80-50 Surface Quality:

24.00 Radius of Curvature (mm):

## Regulatory Compliance

Compliant RoHS 2015:

View Certificate of Conformance:

Compliant Reach 247:

## Product Details

- Ideal for Focusing Light
- Aluminum and Gold Coating Options
- Available in Sizes Ranging from 9 - 50mm

Concave Spherical Mirrors are ideal for collecting and focusing light in a wide range of applications. These mirrors are available with protected metallic coatings covering the UV, VIS, and IR spectrum. A protective layer increases the coating's durability and prevents corrosion. Concave Spherical Mirrors are available in diameters ranging from 9-50mm for ease of system integration.

## Technical Information

