

TECHSPEC® 12mm Dia. x 25mm FL 633nm V-Coat, UV PCX Lens



Stock #34-111 3-5 DAYS

[Other Coating Options](#)

- 1 + **A\$225.60**

ADD TO CART

Qty 1-5
A\$225.60
Qty 6+
A\$180.40
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
12.00 +0.0/-0.025

Effective Focal Length EFL (mm):
25.00 @ 587.6nm

Back Focal Length BFL (mm): 22.31
Coating: Laser V-Coat (633nm)
Coating Specification: R _{abs} <0.25% @ 633nm
Substrate: ☐ Fused Silica (Corning 7980)
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): ≤1
Center Thickness CT (mm): 3.92 ±0.05
Edge Thickness ET (mm): 2.22
Radius R₁ (mm): 11.46
Clear Aperture CA (mm): 11
f/#: 2.08
Numerical Aperture NA: 0.24
Design Wavelength DWL (nm): 633
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Edges: Fine Ground, Protective Bevel as Needed
Damage Threshold, By Design: ☐ 5 J/cm² @ 633nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant