


**TECHSPEC® 12mm Dia. x 30mm FL, NIR I Coated, Plano-Convex Lens**

UV Fused Silica Plano-Convex (PCX) Lenses

Stock #18-045 **6 In Stock**[-](#) [1](#) [+](#) **A\$248<sup>.00</sup>****ADD TO CART**

Volume Pricing	
Qty 1-5	<b>A\$248.00</b> each
Qty 6-25	<b>A\$198.40</b> each
Qty 26-49	<b>A\$187.20</b> each
Need More?	<a href="#">Request Quote</a>

## Product Downloads

**SPECIFICATIONS****General**

Type:

## Physical & Mechanical Properties

	<b>Diameter (mm):</b>
12.00 -0.025	
	<b>Centering (arcmin):</b>
<1	
	<b>Center Thickness CT (mm):</b>
3.55 ±0.05	
	<b>Edge Thickness ET (mm):</b>
2.17	
	<b>Clear Aperture CA (mm):</b>
11	
	<b>Bevel:</b>
Protective as needed	

## Optical Properties

	<b>Effective Focal Length EFL (mm):</b>
30.00 @ 587.6nm	
	<b>Back Focal Length BFL (mm):</b>
27.56	
	<b>Coating:</b>
NIR I (600-1050nm)	
	<b>Coating Specification:</b>
$R_{avg} \leq 0.5\% @ 600 - 1050nm$	
	<b>Substrate:</b> <input type="checkbox"/>
<a href="#">Fused Silica</a> (Corning 7980)	
	<b>Surface Quality:</b>
40-20	
	<b>Power (P-V) @ 632.8nm:</b>
3 Rings	
	<b>Irregularity (P-V) @ 632.8nm:</b>
0.5 Rings	
	<b>Focal Length Tolerance (%):</b>
±1	
	<b>Radius R<sub>1</sub> (mm):</b>
13.75	
	<b>f#:</b>
2.5	
	<b>Numerical Aperture NA:</b>
0.20	
	<b>Wavelength Range (nm):</b>
600 - 1050	
	<b>Damage Threshold, Reference:</b> <input type="checkbox"/>
7 J/cm <sup>2</sup> @ 1064nm, 10ns	

## Regulatory Compliance

	<b>RoHS 2015:</b>
<a href="#">Compliant</a>	
	<b>Certificate of Conformance:</b>
<a href="#">View</a>	
	<b>Reach 235:</b>
<a href="#">Compliant</a>	

## PRODUCT DETAILS

- AR Coated to Provide <0.5% Reflection per Surface for 600 - 1050nm
- Precision Fused Silica Substrate
- Various Coating Options: [Uncoated](#), [MgF<sub>2</sub>](#), [UV-AR](#), [UV-VIS](#), [VIS-EXT](#), [VIS-NIR](#), [VIS 0°](#), [YAG-BBAR](#), and [NIR II](#)

TECHSPEC® UV Fused Silica Plano-Convex (PCX) Lenses NIR I Coated feature precision specifications and a [variety of coating options](#) on a broadband substrate. Fused Silica is commonly used in applications from the Ultraviolet (UV) through the Near-Infrared (NIR). Its low index of refraction, low coefficient of thermal expansion, and low inclusion content make it ideal for laser applications and harsh environmental conditions. TECHSPEC® UV Fused Silica Plano-Convex (PCX) Lenses NIR I Coated feature industry leading diameter and centration specifications, making them ideal for integration into demanding imaging and targeting applications. These lenses are NIR I coated to increase their coating performance in the 600nm to 1050nm range.


## TECHNICAL INFORMATION

### FUSED SILICA

#### Uncoated Fused Silica

[Technical Transmission](#)


### Typical Transmission



Typical transmission of a 3mm thick, uncoated fused silica window across the UV- NIR spectra.

[Click Here to Download Data](#)

### Fused Silica with $\text{MgF}_2$ Coating Typical Transmission



Typical transmission of a 3mm thick fused silica window with  $\text{MgF}_2$  (400-700nm) coating at 0° AOI.


The blue shaded region indicates the coating design wavelength range, with the following specification:

$$R_{\text{avg}} \leq 1.75\% \text{ @ 400 - 700nm (N-BK7)}$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

### Fused Silica with UV-AR Coating Typical Transmission



Typical transmission of a 3mm thick fused silica window with UV-AR (250-425nm) coating at 0° AOI.


The blue shaded region indicates the coating design wavelength range, with the following specification:

$$\begin{aligned} R_{\text{abs}} &\leq 1.0\% \text{ @ 250 - 425nm} \\ R_{\text{avg}} &\leq 0.75\% \text{ @ 250 - 425nm} \\ R_{\text{avg}} &\leq 0.5\% \text{ @ 370 - 420nm} \end{aligned}$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

### Fused Silica with UV-VIS Coating Typical Transmission



Typical transmission of a 3mm thick fused silica window with UV-VIS (250-700nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$$\begin{aligned} R_{\text{abs}} &\leq 1.0\% \text{ @ 350 - 450nm} \\ R_{\text{avg}} &\leq 1.5\% \text{ @ 250 - 700nm} \end{aligned}$$


Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

### Fused Silica with VIS-EXT Coating Typical Transmission



Typical transmission of a 3mm thick fused silica window with VIS-EXT (400-700nm) coating at 0° AOI.




Typical transmission of a 3mm thick fused silica window with VIS-EXT (350-700nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$$R_{avg} \leq 0.5\% @ 350 - 700nm$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)



Typical transmission of a 3mm thick fused silica window with VIS-NIR (400-1000nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:


$$R_{abs} \leq 0.25\% @ 880nm$$

$$R_{avg} \leq 1.25\% @ 400 - 870nm$$

$$R_{avg} \leq 1.25\% @ 890 - 1000nm$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)




Typical transmission of a 3mm thick fused silica window with VIS 0° (425-675nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$$R_{avg} \leq 0.4\% @ 425 - 675nm$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)



Typical transmission of a 3mm thick fused silica window with YAG-BBAR (500-1100nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:


$$R_{abs} \leq 0.25\% @ 532nm$$

$$R_{abs} \leq 0.25\% @ 1064nm$$

$$R_{avg} \leq 1.0\% @ 500 - 1100nm$$

Data outside this range is not guaranteed and is for reference only.


[Click Here to Download Data](#)




Typical transmission of a 3mm thick fused silica window with NIR I (600 - 1050nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$$R < 0.5\% @ 600 - 1050nm$$



### Fused Silica with NIR II Coating Typical Transmission



### CUSTOM

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).