

**TECHSPEC® 12.7 x 6.35mm, 10' Wedge, Mirror Substrate**



TECHSPEC® Laser Mirror Substrates

Stock #21-251 **20+ In Stock**

⊖ 1 ⊕ A\$150<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-10	A\$150.40 each
Qty 11-25	A\$132.80 each
Qty 26-50	A\$116.80 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Laser Mirror Substrate **Type:**

**Physical & Mechanical Properties**

10 ±5 **Parallelism (arcmin):**

80 **Clear Aperture (%):**

Commercial Polish **Back Surface:**

12.70 +0.00/-0.10 **Diameter (mm):**

6.35 ±0.01 **Thickness (mm):**

### Optical Properties

10-5 **Surface Quality:**

$\lambda/10$  **Surface Flatness (P-V):**

Uncoated **Coating:**

[Fused Silica](#) (Corning 7980) **Substrate:**

### Regulatory Compliance

[View](#) **Certificate of Conformance:**

## Product Details

- $\lambda/10$  and  $\lambda/20$  Surface Flatness and 10-5 Surface Quality
- High Quality Fused Silica Substrates
- Imperial Sizes with Circular or Rectangular Geometries
- [Window Substrates](#) Also Available

TECHSPEC® Laser Mirror Substrates are manufactured from high quality fused silica and are designed for use with high power laser sources. These mirrors feature excellent surface specifications, including  $\lambda/10$  and  $\lambda/20$  surface flatness and 10-5 surface quality, to limit the possibility of reduced performance due to surface defects. The high surface quality of these mirror blanks also makes them ideal for use in demanding intra-cavity laser applications. TECHSPEC Laser Mirror Substrates are available in standard imperial sizes, with either circular or rectangular geometries. Please contact us if your application requires a custom size laser mirror substrate.

## Compatible Mounts