

TECHSPEC[®] 12mm Dia. x 100mm FL 785nm V-Coat, UV PCX Lens



Stock **#25-912** 5 In Stock

-

1

+

A\$233^{.60}

ADD TO CART

Volume Pricing	
Qty 1-5	A\$233.60 each
Qty 6-25	A\$185.60 each
Qty 26-49	A\$176.00 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Type:
Plano-Convex Lens

Physical & Mechanical Properties

12.00 +0.0/-0.025	Diameter (mm):
Protective as needed	Bevel:
2.44	Center Thickness CT (mm):
<1	Centering (arcmin):
11	Clear Aperture CA (mm):
2.05	Edge Thickness ET (mm):

Optical Properties

100.00 @ 587.6nm	Effective Focal Length EFL (mm):
Fused Silica	Substrate:
8.33	f/#:
0.06	Numerical Aperture NA:
785nm V-Coat	Coating:
98.33	Back Focal Length BFL (mm):
R _{abs} <0.25% @ 785nm	Coating Specification:
785	Design Wavelength DWL (nm):
±1	Focal Length Tolerance (%):
45.85	Radius R ₁ (mm):
40-20	Surface Quality:
1.5λ	Power (P-V) @ 632.8nm:
λ/4	Irregularity (P-V) @ 632.8nm:

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:

PRODUCT DETAILS

- <0.25% Reflection at 785nm
- 5 - 50mm Diameters Available
- 10 - 250mm EFL Designs Available
- 405nm, 532nm, 1064nm, and 1550nm V-Coated Options Offered

TECHSPEC® Laser Line Coated Fused Silica PCX Lenses are available in a variety of laser line V-Coat AR coating options. Designed for maximum throughput at the specified laser wavelength, these lenses are ideal for applications utilizing low power HeNe, Diode, and Nd:YAG laser sources. With a maximum reflection of <0.25% per surface at the design wavelength, the lenses will provide superior transmission in applications utilizing multiple optical components.