

TECHSPEC® 12mm Dia. x 72mm FL, NIR II Coated, Double-Convex Lens



Stock **#67-628-INK** 10-15 DAYS

[Other Coating Options](#)

-

1

+

A\$84.00

ADD TO CART

Qty 1-9
A\$84.00
Qty 10+
A\$75.60
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
12.00 ±0.025

Back Focal Length BFL (mm):
71.07

Effective Focal Length EFL (mm): 72.00
Coating: NIR II (750-1550nm)
Coating Specification: R_{abs} ≤1.5% @ 750 - 800nm R_{abs} ≤1.0% @ 800 - 1550nm R_{avg} ≤0.7% @ 750 - 1550nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Centering (arcmin): <1
Center Thickness CT (mm): 2.80
Center Thickness Tolerance (mm): ±0.05
Edge Thickness ET (mm): 2.31
Radius R₁=R₂ (mm): 73.97
Clear Aperture CA (mm): 11.00
f/#: 6.00
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1.00
Numerical Aperture NA: 0.08
Type: Double-Convex Lens
Wavelength Range (nm): 750 - 1550
Damage Threshold, By Design: ☐ 8 J/cm² @ 1064nm, 10ns

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View