


[See all 24 Products in Family](#)

12mm Dia x -7.75mm FL Protected Gold Coated, Convex Mirror



Stock **#64-070** **2 In Stock**

⊖ 1 ⊕ A\$83²⁰

ADD TO CART

Volume Pricing	
Qty 1-5	A\$83.20 each
Qty 6-25	A\$75.20 each
Qty 26-49	A\$70.40 each
Need More?	Request Quote

Product Downloads

General

Spherical Mirror **Type:**

Physical & Mechanical Properties

12.00 +0.00/-0.10 **Diameter (mm):**

3.00 **Center Thickness CT (mm):**

90 **Clear Aperture (%)**:

1.79 **Edge Thickness ET (mm)**:

15.50 **Radius R (mm)**:

Optical Properties

-7.75 **Focal Length FL (mm)**:

Protected Gold (700-10000nm) **Coating**:

Coating Specification:
R_{avg} >96% @ 700 - 2000nm
R_{avg} >96% @ 2000 - 10,000nm

Metal **Coating Type**:

±2 **Focal Length Tolerance (%)**:

Substrate:
N-BK7

60-40 **Surface Quality**:

700 - 10000 **Wavelength Range (nm)**:

Damage Threshold, Reference:
0.8 J/cm² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015:
Compliant

Certificate of Conformance:
View

Reach 247:
Compliant

Product Details

- Variety of Diameters and Focal Lengths Available
- Enhanced Aluminum and Protected Gold Coatings
- Ideal for Imaging Systems

Convex Spherical Mirrors feature a polished plano second surface and convex first surface. Used primarily for increasing an imaging system's field of view, convex mirrors create a virtual, upright image. Shorter focal lengths provide wider fields of view, while longer focal lengths provide less distortion. Convex Spherical Mirrors with Enhanced Aluminum coatings are ideal for applications in the visible spectrum, while Protected Gold provides excellent reflection throughout the NIR, MMR, and LWR spectra. The mirrors are offered in 12, 25, and 50mm diameters, in a variety of wavelength ranges.