

TECHSPEC[®] 12mm Dia. x 35mm FL, VIS-NIR Coated, UV Double-Convex Lens



UV Fused Silica Double-Convex (DCX) Lenses



Stock **#63-832** 3-5 DAYS

[Other Coating Options](#)

-

1

+

A\$215.20

ADD TO CART

Qty 1-5

A\$215.20

Qty 6+

A\$172.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
12.00 +0.0/-0.025

Back Focal Length BFL (mm):

33.85
Effective Focal Length EFL (mm): 35.00
Coating: VIS-NIR (400-1000nm)
Coating Specification: R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870nm R _{avg} ≤1.25% @ 890 - 1000nm
Substrate:  Fused Silica (Corning 7980)
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Centering (arcmin): <1
Bevel: Protective bevel as needed
Center Thickness CT (mm): 3.29 ±0.05
Edge Thickness ET (mm): 2.14
Radius R₁=R₂ (mm): 31.57
Clear Aperture CA (mm): 11.00
f/#: 2.92
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Numerical Aperture NA: 0.17
Type: Double-Convex Lens
Wavelength Range (nm): 400 - 1000
Damage Threshold, Reference:  5 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant