

12mm Dia. x 7.5mm FL, Uncoated Molded Aspheric Condenser Lens



Molded Aspheric Condenser Lenses

Stock **#88-284** 3-5 DAYS

[Other Coating Options](#)



1



A\$50.40

ADD TO CART

Qty 1-10

A\$50.40

Qty 11+

A\$44.64

Volume Pricing

[Request Quote](#)

Get Product Downloads

Diameter (mm):
12.00 +/-0.3

Effective Focal Length EFL (mm):
7.50 @ 587.6nm

Numerical Aperture NA:
0.8

Back Focal Length BFL (mm): 4.60
Substrate: Liba2000+
Focal Length Tolerance (%): ±7
Coating: Uncoated
Centering (arcmin): ≤30
Surface Quality: 5/3 x0.4; E 0.2
Clear Aperture CA (mm): 9.50
Edge Thickness ET (mm): 1.85
Center Thickness CT (mm): 5.50 +/-0.20
f/#: 0.63
Bevel: Protective bevel as needed
Diameter of Asphere (mm): 12.0
Radius R₂ (mm): 12.7
Shape of Back Surface: Convex
Type: Condenser Lens
Wavelength Range (nm): 350 - 2000
Conjugate Distance: Infinite
Note: Click here for more information on the ISO 10110 surface quality specification.

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant