

TECHSPEC[®] 12mm, f/8 Ci Series Fixed Focal Length Lens



12mm Focal Length

Stock **#86-611** 20+ In Stock

-

1

+

A\$221⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-24	A\$221.00 each
Qty 25+	A\$200.00 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Ci Series	Series:
Fixed Focal Length Lens	Type:

Physical & Mechanical Properties

	Iris Option:
Fixed	
	Length (mm):
29.00	
	Maximum Diameter (mm):
26.5	
	Outer Diameter (mm):
26.5	
	Weight (g):
31	
	Maximum Rear Protrusion (mm):
0.31	
	Diameter (mm):
26.50	

Optical Properties

Horizontal Field of View @ Max Sensor Format: 80.9mm - 41.2°	
Field of View at Max Sensor Format: Horizontal: 81.3mm - 41.2° Vertical: 60.5mm - 31.3° Diagonal: 102.3mm - 50.5°	
Horizontal Field of View, 2/3" Sensor: 80.9mm - 41.2°	
Horizontal Field of View, 1/1.8" Sensor: 65.8mm - 34.0°	
Horizontal Field of View, 1/2" Sensor: 58.3mm - 30.4°	
Horizontal Field of View, 1/2.5" Sensor: 52.8mm - 27.6°	
Horizontal Field of View, 1/3" Sensor: 43.5mm - 22.9°	
Horizontal Field of View, 1/4" Sensor: 32.6mm - 17.2°	
Maximum Image Circle (mm): 11.00	
Numerical Aperture NA, Object Side: 0.0066	
Number of Elements (Groups): 7 (7)	
Focal Length FL (mm): 12.00	
Working Distance (mm): 100 - ∞	
Aperture (f/#): f/8	
Coating: 425 - 675nm BBAR	
Coating Specification: 425 - 675nm BBAR	
Entrance Pupil Position (mm): 11.01	
Object Space Principal Plane (mm): 17.32	
Image Space Principal Plane (mm): 1.98	
Maximum Distortion (%): -2.09	
Exit Pupil Position (mm): -11.38	
Lens Wavelength Range: VS	

Sensor

	Maximum Sensor Format:
2/3"	
	Pixel Size (µm):
2.74	

Threading & Mounting

	Filter Thread:
M25.5 x 0.50 (Male)	
	Filter Thread Adapter:
#89-941 (Required)	

M22.0 x0.75 (Male)	Front Thread:
C-Mount	Mount:
Environmental & Durability Factors	
-20 to +60	Storage Temperature (°C):
Industrial (Fixed Aperture with Simplified Mechanics)	Type of Ruggedization:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:

PRODUCT DETAILS

These compact lenses are designed specifically for volume integration into applications such as analytical medical devices, including benchtop-based blood analyzers. For customized f/# versions to best suit your instrumentation application needs and to discuss volume requirements, please [contact us](#).


- Up to 2/3", C-Mount Lens
- Up to 7.5 MegaPixels, 2.8µm Pixel Size Sensors
- Instrumentation (Ci) Versions of our C Series Lenses with Streamlined Mechanical Designs and Fixed Apertures
- 3.5mm to 50mm Focal Length
- [Ruggedized \(Cr\) Designs](#) Also Available

TECHSPEC® Ci Series Fixed Focal Length Lenses are a streamlined version of our C Series Fixed Focal Length Lenses. They feature the same low lens-to-lens variation and broadband anti-reflection (BBAR) coating for maximum light transmission, while offering reduced weight and size. An adjustable, lockable focus allows for setting and locking the best focus position for instrumentation integration. TECHSPEC® Ci Series Fixed Focal Length Lenses are designed specifically for volume integration into applications such as factory inspection and automation to benchtop biomedical devices. The Ci Series offers a wide range of aperture options, ensuring maximum flexibility of resolution, throughput, and depth of field.


Edmund Optics has created a family of high performance optical designs (the C Series family) and developed 6 customized optomechanical solutions targeted for specific applications. These lens sub-families utilize the same optics as the C Series lenses providing the same optical performance in a variety of optomechanical solutions to meet your application requirements:

- **C Series:** Features locking cam focus and iris adjustment and is the most adjustable version of these optical designs; they are the typical high quality machine vision lenses. Also available with a [VIS-NIR Broadband Anti-Reflection \(BBAR\) Coating](#).
- **Ci Series:** Simplified mechanics featuring fixed apertures with compact housing. [Industrial Ruggedization](#) for reduced size, cost, and locked focus.
- **Cr Series:** All optics glued in place and a locking C-clamp focus ring. [Stabilized Ruggedization](#) for reduced pixel shift and improved focus stability.
- **Cx Series:** Modular, flexible mechanics allows lenses to be taken apart for easy integration of accessories such as liquid lenses, apertures, and more.
- **Liquid Lens Cx Series:** Designed with an integrated liquid lens for quick autofocus.
- **Cw Series:** Waterproof, designed to meet IEC [Ingress Protection](#) Code IPX7 and IPX9K.


TECHNICAL INFORMATION




#86-611, 12mm, f/8 Ci Series Fixed Focal Length Lens, Distortion Plot




#86-611, 12mm, f/8 Ci Series Fixed Focal Length Lens, Relative Illumination Plot




#86-611, 12mm, f/8 Ci Series Fixed Focal Length Lens, Working Distance versus Field of View Plot




#86-611, 12mm, f/8 Ci Series Fixed Focal Length Lens, Modulated Transfer Function (MTF) Plot, 300mm Working Distance, f8



#86-611, 12mm, f/8 Ci Series Fixed Focal Length Lens, Depth of Field Plot, 300mm Working Distance, f8




#86-611, 12mm, f/8 Ci Series Fixed Focal Length Lens, Modulated Transfer Function (MTF) Plot, 750mm Working Distance, f8



#86-611, 12mm, f/8 Ci Series Fixed Focal Length Lens, Depth of Field Plot, 750mm Working Distance, f8

Focal Length	A	B	C	D
6mm	M34.0 x 0.5	47.8mm	34mm	1.17mm
12mm	M22.0 x 0.75	29.0mm	22mm	0.96mm
16mm	M22.0 x 0.75	40.8mm	22mm	1.09mm
25mm	M22.0 x 0.75	29.9mm	22mm	1.33mm
35mm	M25.5 x 0.5	41mm	22.5mm	3.82mm
50mm	M30.5 x 0.5	49.5mm	30.5mm	2.06mm



COMPATIBLE CAMERAS