

[See all 13 Products in Family](#)

**TECHSPEC® 12mm Dia. x -24mm FL, Uncoated, Double-Concave Lens**



Stock **#48-683** **20+ In Stock**

[Other Coating Options](#)

− 1 + A\$54<sup>40</sup>

**ADD TO CART**

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-9        | A\$54.40 each                 |
| Qty 10-25      | A\$49.20 each                 |
| Qty 26-49      | A\$44.00 each                 |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

**General**

Double-Concave Lens **Type:**

**Physical & Mechanical Properties**

12.00 +0.0/-0.025 **Diameter (mm):**

|                      |                                  |
|----------------------|----------------------------------|
| Protective as needed | Bevel:                           |
| 2.00                 | Center Thickness CT (mm):        |
| ±0.05                | Center Thickness Tolerance (mm): |
| <1                   | Centering (arcmin):              |
| 11.00                | Clear Aperture CA (mm):          |
| 3.31                 | Edge Thickness ET (mm):          |

## Optical Properties

|            |   |
|------------|---|
| -24.00     | Effective Focal Length EFL (mm):            |
| N-BK7      | Substrate: <input type="checkbox"/>         |
| 2.00       | f#:   |
| 0.25       | Numerical Aperture NA:                      |
| Uncoated   | Coating:                                    |
| 350 - 2200 | Wavelength Range (nm):                      |
| -24.65     | Back Focal Length BFL (mm):                 |
| 587.6      | Focal Length Specification Wavelength (nm): |
| ±1         | Focal Length Tolerance (%):                 |
| -25.14     | Radius R <sub>1</sub> =R <sub>2</sub> (mm): |
| 40-20      | Surface Quality:                            |
| 1.5λ       | Power (P-V) @ 632.8nm:                      |
| λ/4        | Irregularity (P-V) @ 632.8nm:               |

## Regulatory Compliance

|           |                             |
|-----------|-----------------------------|
| Compliant | RoHS 2015:                  |
| Compliant | Reach 219:                  |
| View      | Certificate of Conformance: |

### Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- Wavelength Range of 350-2200nm
- Precision Diameter and Centration Tolerances Allow for Easy OEM Integration
- Wide Variety of Diameters and Focal Lengths
- Additional AR Coating Options Available: [VIS-EXT](#), [MgF<sub>2</sub>](#), [VIS 0°](#), [VIS-NIR](#), [NIR I](#), and [NIR II](#)

TECHSPEC® Uncoated Double-Concave (DCV) Lenses are designed to have two inward curved surfaces and a negative focal length similar to Plano-Concave (PCV) lenses. These lenses can be used for balancing aberrations created by other lenses within a system due to their negative spherical aberration. Double-Concave (DCV) lenses are commonly used in a variety of applications including image reduction, beam expansion and telescopes. TECHSPEC® Uncoated Double-Concave (DCV) Lenses offer optimal performance in the 350nm to 2200nm range. These lenses are also available [VIS-EXT](#), [MgF<sub>2</sub>](#), [VIS 0°](#), [VIS-NIR](#), [NIR I](#), or with [NIR II](#) AR coating options.

## Technical Information



## Compatible Mounts