



[See all 6 Products in Family](#)

150 x 150mm 38% Transmission Linear Polarizing Film (XP38)



Stock **#20-240** 20+ In Stock

-

1

+

A\$73²⁰

ADD TO CART

Volume Pricing	
Qty 1-10	A\$73.20 each
Qty 11-25	A\$60.80 each
Need More?	Request Quote

Product Downloads

General	
Linear Polarizer	Type:
	Note:
Polarization axis can be identified as follows: Circular Parts - Parallel to direction of notch on polarizer Square Parts - Parallel to mark on protective film Rectangular Parts - Parallel to first listed dimension	

Physical & Mechanical Properties	
5.91 x 5.91	Dimensions (inches):
150.0 x 150.0	Dimensions (mm):
0.007 ±0.001	Thickness (inches):
0.19 ±0.02	Thickness (mm):
±1.0	Dimensional Tolerance (mm):
Polarizing Film	Construction:

Optical Properties	
Up to 7,500:1	Extinction Ratio:
Polymer Film XP38	Substrate: □
Single: 38.5 ±2 Parallel: 30.1 Crossed: <0.004	Transmission (%):
400 - 700	Wavelength Range (nm):
>99.98	Polarization Efficiency (%):
<±5	Transmission Variance after 1000 Hours (%):

Environmental & Durability Factors	
-20 to +70	Operating Temperature (°C):
70 x 240	Heat Resistance (°C x Hours):
40 x 95% RH x 240	Humidity Resistance (°C x Hours):

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:


Product Details

- 38% Transmission of Unpolarized Light from 400 – 700nm
- Extinction Ratio of up to 7500:1
- Excellent Cost to Performance Ratio

Commercial Grade Visible Linear Polarizing Film (XP38) is a high quality, neutral gray polymer polarizing film that provides a balance between high transmission and high extinction ratio. Offering 38% transmission of unpolarized light and an extinction ratio up to 7500:1 in the visible spectrum, this polarizing film is ideal for a range of imaging, microscopy and display applications. Available in sheets up to 600 x 900mm, Commercial Grade Visible Linear Polarizing Film (XP38) can be cut to fit any application need.

Note: The transmission axis is parallel to the first dimension listed.

Technical Information



Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).
