

[See all 65 Products in Family](#)

TECHSPEC® 12mm, f/4 Cw Series Fixed Focal Length Lens



12mm Focal Length



Stock #15-633 **20+ In Stock**

- 1 + A\$346.⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	A\$346.00 each
Need More?	Request Quote

Product Downloads

General

Cw Series **Product Family:**

C-Mount compatible with O-ring 25mm ID x2mm **Note:**

Fixed Focal Length Lens **Type:**

Physical & Mechanical Properties

Fixed Iris Option:

38.10

Length (mm):

36

Outer Diameter (mm):

0.6

Maximum Rear Protrusion (mm):

0.6

Optical Properties

Field of View at Max Sensor Format:

Horizontal: 41.0°

Vertical: 31.3°

Diagonal: 50.5°

Horizontal Field of View, 2/3" Sensor:

41.0°

Horizontal Field of View, 1/1.8" Sensor:

33.8°

Horizontal Field of View, 1/2" Sensor:

30.2°

Horizontal Field of View, 1/2.5" Sensor:

27.4°

Horizontal Field of View, 1/3" Sensor:

22.8°

Horizontal Field of View, 1/4" Sensor:

17.1°

Maximum Image Circle (mm):

11.00

Numerical Aperture NA, Object Side:

0.0118

Number of Elements (Groups):

7 (7)

Focal Length FL (mm):

12.00

Working Distance (mm):

100 - ∞

Aperture (f#):

f/4

Coating Specification:

425 - 675nm BBAR

Entrance Pupil Position (mm):

17.6208

Object Space Principal Plane (mm):

23.93

Image Space Principal Plane (mm):

1.98

Maximum Distortion (%):

2.11

Exit Pupil Position (mm):

-11.3801

Lens Wavelength Range:

VS

Sensor

Maximum Sensor Format:

2/3"

Pixel Size (μm):

2.74

Threading & Mounting

Filter Thread:

M30.5 x 0.50 (Female)

Mount:

C-Mount

Environmental & Durability Factors

Environmental Rating:

IPX7 and IPX9K

Storage Temperature (°C):

-20 to +60

Type of Ruggedization:

Waterproof (IPX7 and IPX9K)

Regulatory Compliance

Product Details


- Up to 2/3", C-Mount Lens
- Waterproof (Cw) Versions of C Series Fixed Focal Length Lenses
- Meets IEC Ingress Protection Ratings of IPX7 and IPX9K
- Designed to Eliminate the Need for a Protective Lens Cover

TECHSPEC® Cw Series Fixed Focal Length Lenses are waterproof versions of our [TECHSPEC® C Series Fixed Focal Length Lenses](#). Designed to meet IEC Ingress Protection Codes IPX7 and IPX9K, these lenses withstand exposure to water up to 1 meter depth for 30 minutes and operate in close-range high pressure, high temperature water spray downs with the exception of all 3.5 and 4.5mm options which are IPX7. These lenses include a hydrophobic coated window to prevent water droplets from settling on the lens' surface. To prevent moisture from entering the housing, the lenses are sealed with multiple O-rings. TECHSPEC® Cw Series Fixed Focal Length Lenses are designed for up to 7.5 MegaPixel, 2/3" sensors and are ideal for applications including food, pharma, automotive, and security. These lenses won the Bronze-Level 2021 Vision Systems Design Innovators Award.


Edmund Optics has created a family of high performance optical designs (the C Series family) and developed 6 customized optomechanical solutions targeted for specific applications. These lens sub-families utilize the same optics as the C Series lenses providing the same optical performance in a variety of optomechanical solutions to meet your application requirements:

- **C Series:** Features locking cam focus and iris adjustment and is the most adjustable version of these optical designs; they are the typical high quality machine vision lenses. Also available with a [VIS-NIR Broadband Anti-Reflection \(BBAR\) Coating](#).
- **Ci Series:** Simplified mechanics featuring fixed apertures with compact housing. [Industrial Ruggedization](#) for reduced size, cost, and locked focus.
- **Cr Series:** All optics glued in place and a locking C-clamp focus ring. [Stabilized Ruggedization](#) for reduced pixel shift and improved focus stability.
- **Cx Series:** Modular, flexible mechanics allows lenses to be taken apart for easy integration of accessories such as liquid lenses, apertures, and more.
- **Liquid Lens Cx Series:** Designed with an integrated liquid lens for quick autofocus.
- **Cw Series:** Waterproof, designed to meet IEC [Ingress Protection](#) Code IPX7 and IPX9K.


Technical Information




#15-633, 12mm, f/4 Cw Series Fixed Focal Length Lens, Distortion Plot




#15-633, 12mm, f/4 Cw Series Fixed Focal Length Lens, Relative Illumination Plot




#15-633, 12mm, f/4 Cw Series Fixed Focal Length Lens, Working Distance versus Field of View Plot




#15-633, 12mm, f/4 Cw Series Fixed Focal Length Lens, Modulated Transfer Function (MTF) Plot, 300mm Working Distance, f4



#15-633, 12mm, f/4 Cw Series Fixed Focal Length Lens, Depth of Field Plot, 300mm Working Distance, f4



#15-633, 12mm, f/4 Cw Series Fixed Focal Length Lens, Modulated Transfer Function (MTF) Plot, 750mm Working Distance, f4



#15-633, 12mm, f/4 Cw Series Fixed Focal Length Lens, Depth of Field Plot, 750mm Working Distance, f4