

**TECHSPEC® 1300nm 12.5mm Diameter, OD 4.0 Shortpass Filter**



High Performance OD 4.0 Shortpass Filters

Stock **#89-672** 3-5 DAYS

⊖ 1 ⊕

**A\$334.40**

ADD TO CART

Qty 1-5

**A\$334.40**

Qty 6+

**A\$267.20**

Volume Pricing

[Request Quote](#)

Get Product Downloads



**Diameter (mm):**  
12.50 +0.0/-0.2

**Angle of Incidence (°):**  
0

**Optical Density OD (Average):**  
≥4.0

|                                                                                                                                                                                     |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Cut-Off Wavelength (nm):</b><br>1,300.00                                                                                                                                         |
| <b>Substrate:</b> <br><a href="#">Fused Silica</a> (Corning 7980)                                  |
| <b>Coating:</b><br>Hard Coated                                                                                                                                                      |
| <b>Rejection Wavelength (nm):</b><br>1340 - 1650                                                                                                                                    |
| <b>Surface Quality:</b><br>60-40                                                                                                                                                    |
| <b>Thickness (mm):</b><br>3.00                                                                                                                                                      |
| <b>Thickness Tolerance (mm):</b><br>±0.1                                                                                                                                            |
| <b>Transmission (%):</b><br>≥91                                                                                                                                                     |
| <b>Transmission Wavelength (nm):</b><br>600 - 1285                                                                                                                                  |
| <b>Type:</b><br>Shortpass Filter                                                                                                                                                    |
| <b>Clear Aperture (%):</b><br>>80                                                                                                                                                   |
| <b>Transmitted Wavefront, RMS:</b><br>≤λ/4 @ 633nm (prior to coating)                                                                                                               |
| <b>Slope Factor (%):</b><br><1                                                                                                                                                      |
| <b>Cut-Off Tolerance (%):</b><br>±1                                                                                                                                                 |
| <b>Environmental Durability:</b><br>Humidity per MIL-STD-810H, Section 507.6<br>Temperature per MIL-STD-810H, Section 501.7 and 502.7                                               |
| <b>Physical Durability:</b><br>Adhesion per MIL-PRF-13830B, Section C.4.5.12<br>Moderate abrasion per MIL-PRF-13830B, Section C.4.5.11<br>Cleaning per MIL-C-48497A Section 4.5.4.2 |
| <b>Note:</b><br>Arrow on part indicates filter coated surface.                                                                                                                      |
| <b>Wavelength Range (nm):</b><br>600 - 1650                                                                                                                                         |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 240:</b><br><a href="#">Compliant</a>             |