

TECHSPEC[®] 15.0mm Dia. x 30.0mm FL, MgF₂ Coated, Plano-Convex Lens



Stock **#31-856** 3-5 DAYS

[Other Coating Options](#)

-

1

+

A\$56.00

ADD TO CART

Qty 1-9

A\$56.00

Qty 10+

A\$50.40

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
15.00 +0.0/-0.025

Effective Focal Length EFL (mm):
30.00 @ 587.6nm

Back Focal Length BFL (mm): 27.90
Coating: MgF ₂ (400-700nm)
Coating Specification: R _{avg} ≤1.75% @ 400 - 700nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 3.18 ±0.10
Edge Thickness ET (mm): 1.25
Radius R₁ (mm): 15.52
Clear Aperture CA (mm): 14
f/#: 2
Numerical Aperture NA: 0.25
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 400 - 700
Damage Threshold, Reference: ☐ 10 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View