

## 1.5" Length, 8-32 and 1/4-20, Steel Post



Stock #72-782 NEW 20+ In Stock

-

1

+

A\$9<sup>60</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | A\$9.60 each                  |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

### SPECIFICATIONS

#### General

English

Type:

#### Physical & Mechanical Properties

12.7

Diameter (mm):

|                                      |                             |
|--------------------------------------|-----------------------------|
| 0.5                                  | Diameter (inches):          |
| 38.1                                 | Length (mm):                |
| 1.5                                  | Length (inches):            |
| Threading & Mounting                 |                             |
| Thread 1: 8-32<br>Thread 2: 1/4 - 20 | Male Thread:                |
| Regulatory Compliance                |                             |
| Compliant                            | RoHS 2015:                  |
| View                                 | Certificate of Conformance: |
| Compliant                            | Reach 247:                  |

## PRODUCT DETAILS

- English or Metric Versions Options Available
- Wide Variety of Lengths Available from 25.4 to 304.8mm (1" to 12").
- Removable Top and Bottom Set Screws Available

Stainless Steel Optical Mounting Posts are a practical and straightforward way to integrate optical assemblies and photonic equipment onto an [optical lab table](#) or [breadboard](#). All mounting posts are 12.7 mm (0.5") in diameter and are offered in various lengths from 25.4 to 304.8mm (1" to 12"). Each mounting post features a female thread on each end with a set screw preinstalled, making it simple to mount components with counterbore or tapped hole mounting features. Stainless Steel Optical Mounting Posts can be used with [Post Holders](#) to allow for height adjustment of the optical component, and for a secure connection with the optical benchtop. Thread values (M4 x 0.7/M6 x 1.0 for Metric; 8-32/1/4-20 for English) are laser-engraved on the ends of each post for quick identification and integration.

**Note:** All posts have a through-hole that allows an Allen wrench, 5.5mm or 7/32" keysize, or other tools to rotate the post easily.