



1

A\$4,771.20

A\$4,771.20

A\$4,294.40

[Request Quote](#)

N20

56.2

Uncoated

Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 0.1
Diameter (mm): 152.40 +0.00/-1.00
Thickness (mm): 25.40 ±2.0
Diameter (inches): 6.00 +0.00/-0.04
Thickness (inches): 1.00 ±0.08
Clear Aperture CA (mm): 137.20
Color: Yellow Tint
Construction: Single Surface
Density (g/cm³): 2.53
Index of Refraction n_d: 1.542
Knoop Hardness (kg/mm²): 620
Parallelism (arcmin): ≤3
Poisson's Ratio: 0.24
Substrate: ZERODUR®
Surface Quality: 60-40
Type: Interferometry Window
Young's Modulus (GPa): 90.3
Bevel: Protective as needed

Regulatory Compliance

RoHS 2015: Compliant
Reach 211: Compliant
Certificate of Conformance: View