

TECHSPEC[®] 15mm 355nm, Laser Line λ /20 High Tolerance Right Angle Mirror



Stock #37-649 3-5 DAYS

-

1

+

A\$395.20

ADD TO CART

Qty 1-5
A\$395.20
Qty 6+
A\$316.00
Volume Pricing
Request Quote

Get Product Downloads



Surface Flatness (P-V):
 λ /20

Substrate: [Fused Silica](#) (Corning 7980)

Surface Quality:
20-10

Length of Legs (mm):

15.00
Dimensional Tolerance (mm): +0.00/-0.10
Coating Specification: R _{abs} >99.8% @ 355nm @ 45° AOI R _{avg} >99.5% @ 351 - 358nm @ 45° AOI
Coating: Laser Mirror (355nm)
Bevel: Protective bevel as needed
Clear Aperture (%): 90
Design Wavelength DWL (nm): 355
Length of Hypotenuse (mm): 21.20
Type: Right Angle Mirror
Pyramid Tolerance (arcmin): ±1
Angle Tolerance (arcsec): ±15
Damage Threshold, Reference:  1MW/cm ² @ 355nm

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View