

TECHSPEC[®] 15mm Dia 0.38 NA, UV Coated, UV Fused Silica Aspheric Lens



TECHSPEC UV Fused Silica Aspheric Lenses



Stock **#49-694** 3-5 DAYS

[Other Coating Options](#)

-

1

+

A\$784.00

ADD TO CART

Qty 1-5

A\$784.00

Qty 6+

A\$627.20

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
15.00 +0.0/-0.1

Effective Focal Length EFL (mm):

20.00 @ 587.6nm
Numerical Aperture NA: 0.38
Back Focal Length BFL (mm): 15.89
Substrate: ☐ Fused Silica (Corning 7980)
Aspheric Design Wavelength (nm): 587.6
Asphere Figure Error, RMS @ 632.8nm: 1.2λ
Coating: UV (250-425nm)
Coating Specification: R _{avg} ≤1.5% @ 250 - 425nm
Centering (arcmin): ≤5
Surface Quality: 60-40
Clear Aperture CA (mm): 13.5
Edge Thickness ET (mm): 2.68
Center Thickness CT (mm): 6.00 ±0.1
f/#: 1.33
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Wavelength Range (nm): 250 - 425
Conjugate Distance: Infinite
Power (diopters): 50.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant