

[See all 72 Products in Family](#)

TECHSPEC® 15mm Dia. Linear Polarizing Film (XP42-70)



Stock #71-360 **20+ In Stock**

- 1 + A\$30⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-10	A\$30.40 each
Qty 11-25	A\$25.12 each
Need More?	Request Quote

Product Downloads

General

Linear Polarizer **Type:**

Polarization axis is parallel to notch on polarizer edge **Note:**

Physical & Mechanical Properties

15.00 +0.0/-0.3 **Diameter (mm):**

0.72 ±0.1 **Thickness (mm):**

Polarizing Film on PMMA

Construction:

Optical Properties

Uncoated, protective film on both sides

Coating:

9000:1 (nominal at 555nm)

Extinction Ratio:

Substrate:

Polymer Film XP42-40

Transmission (%):

Single: 42 ±2
Parallel: 36.4
Crossed: <0.004 (nominal at 555nm)

400 - 700

Wavelength Range (nm):

>99.98 (nominal at 555nm)

Polarization Efficiency (%):

42 ±2

Transmission, Single (%):

36.4

Transmission, Parallel (%):

<0.004 (nominal at 555nm)

Transmission, Crossed (%):

Environmental & Durability Factors

-10 to +60

Operating Temperature (°C):

Regulatory Compliance

[View](#)

Certificate of Conformance:

Product Details

- High Transmission of Unpolarized Light from 400 – 700nm
- Excellent Extinction Ratio of 9000:1
- Available in Custom Sizes
- [High-Temperature](#) Options Also Available



Ideal for a range of imaging applications, TECHSPEC® High Contrast Linear Polarizing Film (XP42) features an excellent extinction ratio and high transmission from 400 – 700nm. This polarizing film is offered in multiple thicknesses; thicker polarizing film has increased rigidity. Available in sheets, TECHSPEC® High Contrast Linear Polarizing Film (XP42) can be cut to fit any application need.

Note: Polarizer Film with adhesive available.

Immediate Custom Quotes Available

If you have a need for any round, square, or rectangular size of a TECHSPEC High Contrast Linear Polarizing Film (XP42) in dimensions between 3mm and 600mm, please visit our [Polarizing Film Tool](#). We'll provide an immediate quote, and can deliver the part to your requested size in approximately 3 weeks. A full list of standard manufacturing tolerances and restrictions are listed. For fully customized polymer polarizers to your requirements, visit our [Customized Polymer Polarizers Capabilities](#) page.

Technical Information



XP44 - Linear Polarizer

