

**TECHSPEC® 15mm 850nm, Laser Line Polarizing Cube Beamsplitter**



TECHSPEC Laser Line Polarizing Cube Beamsplitters

Stock **#47-049** **20+ In Stock**

⊖ 1 ⊕ **A\$496<sup>00</sup>**

**ADD TO CART**

Volume Pricing	
Qty 1-5	<b>A\$496.00</b> each
Qty 6-25	<b>A\$401.60</b> each
Qty 26-99	<b>A\$364.80</b> each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Linear Polarizer **Type:**

**Physical & Mechanical Properties**

Protective as needed **Bevel:**

90.00 **Clear Aperture (%):**

Cube **Construction:**

15.0 x 15.0 x 15.0 ±0.1 **Dimensions (mm):**

## Optical Properties

±3 **Beam Deviation (arcmin):**

$R_{\text{abs}} < 0.25\%$  @ 850nm **Coating Specification:**

850 **Design Wavelength DWL (nm):**

1000:1 **Extinction Ratio:**

>95 **P-Polarization Transmission (%):**

>99.5 **S-Polarization Reflection (%):**

**N-BK7** **Substrate:**

40-20 **Surface Quality:**

1.25 **Power (fringes) @ 632.8nm:**

0.25 **Irregularity (fringes) @ 632.8nm:**

## Regulatory Compliance

**Compliant** **RoHS 2015:**

**Compliant** **Reach 219:**

**View** **Certificate of Conformance:**

## Product Details

- Designed for Common Diode, Gas, and Solid State Lasers
- Reflects S-Polarized Light, Transmits P-Polarized Light
- High Extinction Ratio

TECHSPEC® Laser Line Polarizing Cube Beamsplitters split randomly polarized beams into two orthogonal, linearly polarized components. S-polarized light is reflected at a 90° angle, while P-polarized light is transmitted. The beamsplitters consist of a pair of precision **right angle prisms** cemented together to minimize transmitted wavefront distortion, and to provide excellent parallelism between incoming and transmitted beams. TECHSPEC® Laser Line Polarizing Cube Beamsplitters are designed for many common laser wavelengths and have a high extinction ratio. These beamsplitters are designed for common diode, gas, and solid-state laser applications.

**LASER OPTICS** MADE BY EDMUND OPTICS®

**LEARN MORE**

## Technical Information

