

TECHSPEC® 15mm, Alum. & AR Coated, N-SF11 Micro Right Angle Prism



N-SF11 Right Angle Prisms

Stock #47-927 3-5 DAYS

⊖ 1 ⊕ **A\$296.00**

ADD TO CART

Qty 1-5

A\$296.00

Qty 6+

A\$266.40

Volume Pricing

[Request Quote](#)

Get Product Downloads



Coating:
MgF₂ & Aluminized

Substrate:
[N-SF11](#)

Surface Quality:
20-10

Type:
Right Angle Prism

Dimensional Tolerance (mm):
+0/-0.1

Angle Tolerance (arcmin):
±2

Bevel:
Protective bevel as needed

Length of Hypotenuse (mm):
21.20

Length of Legs (mm):
15.00

Image Orientation:
Left-Handed

Coating Specification:
Legs: $R_{avg} \leq 1.75\%$ @ 400 - 700nm
Hypotenuse: $R_{avg} > 85\%$ @ 400 - 700nm w/Black
Overpaint

Ray Deviation (°):
90

Wavelength Range (nm):
400 - 700

Damage Threshold, By Design:
Hypotenuse: 0.3 J/cm^2 @ 532nm & 1064nm, 10ns
Legs: 10 J/cm^2 @ 532nm, 10ns

Power (fringes) @ 632.8nm:
1.25

Irregularity (fringes) @ 632.8nm:
0.25

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 235:
[Compliant](#)