

TECHSPEC[®] 15mm Dia., 0.40 Numerical Aperture VIS Coated, Aspheric Lens



Stock **#49-099** 3-5 DAYS

[Other Coating Options](#)

-

1

+

A\$392.00

ADD TO CART

Qty 1-5

A\$392.00

Qty 6+

A\$313.60

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
15.00 +0.0/-0.1

Effective Focal Length EFL (mm):
18.75 @ 587.6nm

Numerical Aperture NA:
0.40

Back Focal Length BFL (mm): 15.92
Substrate: L-BAL35
Aspheric Design Wavelength (nm): 587.6
Asphere Figure Error, RMS @ 632.8nm: 1.2λ
Coating: BBAR (425-675nm)
Coating Specification: R _{avg} ≤1.5% @ 425 - 675nm
Centering (arcmin): ≤5
Surface Quality: 60-40
Clear Aperture CA (mm): 13.5
Edge Thickness ET (mm): 1.82
Center Thickness CT (mm): 4.50 ±0.1
f/#: 1.25
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Wavelength Range (nm): 425 - 675
Conjugate Distance: Infinite
Power (diopters): 53.33

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant