

TECHSPEC®

15mm Dia. x 25mm FL, VIS-EXT Coated, Double-Convex Lens



Stock **#89-160** [CONTACT US](#)

[Other Coating Options](#)

-

1

+

A\$72.00

ADD TO CART

Qty 1-9
A\$72.00
Qty 10+
A\$64.80
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
15.00 +0.000/-0.025

Back Focal Length BFL (mm):
23.82

Effective Focal Length EFL (mm):

25.00
Coating: VS-EXT (350-700nm)
Coating Specification: R _{avg} <0.5% @ 350 - 700nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Centering (arcmin): <1
Bevel: Protective bevel as needed
Center Thickness CT (mm): 3.50
Center Thickness Tolerance (mm): ±0.10
Edge Thickness ET (mm): 1.22
Radius R₁=R₂ (mm): 25.23
Clear Aperture CA (mm): 14.00
f/#: 1.67
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Numerical Aperture NA: 0.30
Type: Double-Convex Lens
Wavelength Range (nm): 350 - 700

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant