


[See all 6 Products in Family](#)

15mm Dia. Mirror, Protected Silver, Optotune Dual Axis Fast Steering Mirror with Position Feedback

See More by [Optotune](#)



Stock **#14-574** CLEARANCE CONTACT US

⊖ 1 ⊕ **A\$4,944⁰⁰**

ADD TO CART

Volume Pricing	
Qty 1+	A\$4,944.00 each
Need More?	Request Quote

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

General

Model Number:
MR-15-30-PS-25x25D

Note:
Do not connect or disconnect the mirror head while the base unit is connected to power as this will

damage the mirror driver.

Physical & Mechanical Properties

15.00 **Diameter (mm):**

2 **Step Response 0.1° (ms):**

12 **Step Response 20° (ms):**

45 **Housing Diameter (mm):**

±25 **Mechanical Tilt (°):**

30 - 100 RMS **Repeatability (µrad):**

Optical Properties

Protected Silver **Coating:**

60-40 **Surface Quality:**

±25 (Mechanical)
±50 (Optical) **Scan Angle (°):**

R_{avg} >94% @400 - 2000nm **Coating Specification:**

Hardware & Interface Connectivity

15 - 28 VDC **Power Requirement:**

Windows® 10 **Operating System:**

Power Supply:
Power Supply Required and Sold Separately:
USA: [#14-576](#)
Europe: [#14-576](#)
Japan: Not Available
Korea: Not Available
China: [#14-576](#)

Environmental & Durability Factors

0 to +40 **Operating Temperature (°C):**

-40 to +85 **Storage Temperature (°C):**

Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[Compliant](#) **Reach 224:**

[View](#) **Certificate of Conformance:**

Product Details

- ±50° of Optical Scanning
- Protected Gold or Silver, and VIS Dielectric Coated Mirror Options
- Compact 45mm Diameter Housing Footprint
- Control via USB, SPI, or Analog Input

Optotune Fast Steering Mirrors provide a larger optical scanning range and mirror size than conventional galvanometers or micro-electro-mechanical (MEMS) mirrors. This dual axis voice-coil mirror (VCM) has a compact footprint with a large 15mm mirror that can be adjusted with ±25° of mechanical tilt for ±50° of optical scanning range. The mirror is operated using the [Optotune Cockpit GUI](#) via USB, serial peripheral interface (SPI), or analog input. Optotune Fast Steering Mirrors are available with a protected silver or gold, and VIS dielectric coating, enabling their use in both visible and near-infrared (NIR) applications. Typical applications for these fast steering mirrors include automotive LiDAR, biometric eye tracking, and field of view expansion of vision systems.

Note: [#14-574](#), [#14-575](#), and [#18-281](#) require [#14-576](#) for operation and [#73-039](#), [#73-042](#), and [#73-043](#) require [#73-038](#) for operation. A heatsink is included with each mirror and recommended to be used to ensure proper heat-dissipation. Do not connect or disconnect the mirror head while the base unit is connected to power as this will damage the mirror driver.