

TECHSPEC®

15mm Dia. x 60mm FL, NIR I Inked, Double-Convex Lens



Stock **#63-642-INK** 10-15 DAYS
[Other Coating Options](#)

-

1

+

A\$84.00

ADD TO CART

Qty 1-9
A\$84.00
Qty 10+
A\$75.60
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
15.00 ±0.025

Back Focal Length BFL (mm):
59.00

Effective Focal Length EFL (mm): 60.00
Coating: NIR I (600-1050nm)
Coating Specification: R _{avg} ≤0.5% @ 600 - 1050nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Centering (arcmin): <1
Bevel: Protective bevel as needed
Center Thickness CT (mm): 3.00
Center Thickness Tolerance (mm): ±0.10
Edge Thickness ET (mm): 2.08
Radius R₁=R₂ (mm): 61.50
Clear Aperture CA (mm): 14.00
f/#: 4.00
Focal Length Specification Wavelength (nm): 587.6
Numerical Aperture NA: 0.13
Type: Double-Convex Lens
Wavelength Range (nm): 600 - 1050
Damage Threshold, By Design: ☐ 7 J/cm² @ 1064nm, 10ns

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View