

**TECHSPEC® 16mm, f/11 Cw Series Fixed Focal Length Lens**



16mm Focal Length



Stock **#15-644** [CONTACT US](#)

- 1 + **A\$346<sup>00</sup>**

**ADD TO CART**

Volume Pricing	
Qty 1+	<b>A\$346.00</b> each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Cw Series **Product Family:**

C-Mount compatible with O-ring 25mm ID x2mm **Note:**

Fixed Focal Length Lens **Type:**

**Physical & Mechanical Properties**

Fixed	<b>Iris Option:</b>
48.60	<b>Length (mm):</b>
37.77	<b>Maximum Diameter (mm):</b>
34.1	<b>Outer Diameter (mm):</b>
1.9	<b>Maximum Rear Protrusion (mm):</b>
38.00	<b>Diameter (mm):</b>

## Optical Properties

65.5mm - 27.8°	<b>Horizontal Field of View @ Max Sensor Format:</b>
Horizontal: 31° Vertical: 23.4° Diagonal: 38.2°	<b>Field of View at Max Sensor Format:</b>
27.8°	<b>Horizontal Field of View, 2/3" Sensor:</b>
22.9°	<b>Horizontal Field of View, 1/1.8" Sensor:</b>
20.4°	<b>Horizontal Field of View, 1/2" Sensor:</b>
18.5°	<b>Horizontal Field of View, 1/2.5" Sensor:</b>
15.3°	<b>Horizontal Field of View, 1/3" Sensor:</b>
11.5°	<b>Horizontal Field of View, 1/4" Sensor:</b>
11.00	<b>Maximum Image Circle (mm):</b>
0.0055	<b>Numerical Aperture NA, Object Side:</b>
7 (6)	<b>Number of Elements (Groups):</b>
16.00	<b>Focal Length FL (mm):</b>
100 - ∞	<b>Working Distance (mm):</b>
f/11	<b>Aperture (f#):</b>
425 - 675nm BBAR	<b>Coating:</b>
425 - 675nm BBAR	<b>Coating Specification:</b>
23.03	<b>Entrance Pupil Position (mm):</b>
25.15	<b>Object Space Principal Plane (mm):</b>
-3.00	<b>Image Space Principal Plane (mm):</b>
-0.77	<b>Maximum Distortion (%):</b>
-5.43	<b>Exit Pupil Position (mm):</b>
VS	<b>Lens Wavelength Range:</b>

## Sensor

2/3"	<b>Maximum Sensor Format:</b>
2.74	<b>Pixel Size (μm):</b>

## Threading & Mounting

M30.5 x 0.50 (Female)	<b>Filter Thread:</b>
C-Mount	<b>Mount:</b>

## Environmental & Durability Factors

**Environmental Rating:**  
IPX7 and IPX9K

**Storage Temperature (°C):**  
-20 to +60

**Type of Ruggedization:**  
Waterproof (IPX7 and IPX9K)

## Regulatory Compliance

**Certificate of Conformance:**  
[View](#)

## Product Details


- Up to 2/3", C-Mount Lens
- Waterproof (Cw) Versions of C Series Fixed Focal Length Lenses
- Meets IEC Ingress Protection Ratings of IPX7 and IPX9K
- Designed to Eliminate the Need for a Protective Lens Cover

TECHSPEC® Cw Series Fixed Focal Length Lenses are waterproof versions of our [TECHSPEC® C Series Fixed Focal Length Lenses](#). Designed to meet IEC Ingress Protection Codes IPX7 and IPX9K, these lenses withstand exposure to water up to 1 meter depth for 30 minutes and operate in close-range high pressure, high temperature water spray downs with the exception of all 3.5 and 4.5mm options which are IPX7. These lenses include a hydrophobic coated window to prevent water droplets from settling on the lens' surface. To prevent moisture from entering the housing, the lenses are sealed with multiple O-rings. TECHSPEC® Cw Series Fixed Focal Length Lenses are designed for up to 7.5 MegaPixel, 2/3" sensors and are ideal for applications including food, pharma, automotive, and security. These lenses won the Bronze-Level 2021 Vision Systems Design Innovators Award.


Edmund Optics has created a family of high performance optical designs (the C Series family) and developed 6 customized optomechanical solutions targeted for specific applications. These lens sub-families utilize the same optics as the C Series lenses providing the same optical performance in a variety of optomechanical solutions to meet your application requirements:

- **C Series:** Features locking cam focus and iris adjustment and is the most adjustable version of these optical designs; they are the typical high quality machine vision lenses. Also available with a [VIS-NIR Broadband Anti-Reflection \(BBAR\) Coating](#).
- **Ci Series:** Simplified mechanics featuring fixed apertures with compact housing. [Industrial Ruggedization](#) for reduced size, cost, and locked focus.
- **Cr Series:** All optics glued in place and a locking C-clamp focus ring. [Stabilized Ruggedization](#) for reduced pixel shift and improved focus stability.
- **Cx Series:** Modular, flexible mechanics allows lenses to be taken apart for easy integration of accessories such as liquid lenses, apertures, and more.
- **Liquid Lens Cx Series:** Designed with an integrated liquid lens for quick autofocus.
- **Cw Series:** Waterproof, designed to meet IEC [Ingress Protection](#) Code IPX7 and IPX9K.


## Technical Information




#15-644, 16mm, f/11 Cw Series Fixed Focal Length Lens, Distortion Plot




#15-644, 16mm, f/11 Cw Series Fixed Focal Length Lens, Relative Illumination Plot




#15-644, 16mm, f/11 Cw Series Fixed Focal Length Lens, Working Distance versus Field of View Plot




#15-644, 16mm, f/11 Cw Series Fixed Focal Length Lens, Modulated Transfer Function (MTF) Plot, 200mm Working Distance, f11



#15-644, 16mm, f/11 Cw Series Fixed Focal Length Lens, Depth of Field Plot, 200mm Working Distance, f11



#15-644, 16mm, f/11 Cw Series Fixed Focal Length Lens, Modulated Transfer Function (MTF) Plot, 500mm Working Distance, f11



#15-644, 16mm, f/11 Cw Series Fixed Focal Length Lens, Depth of Field Plot, 500mm Working Distance, f11