

6X (18.6 - 111mm FL) C-Mount, Close Focus Zoom Lens



10X (13 - 130mm FL) C-Mount, Close Focus Zoom Lens, #54-363

Stock **#70-748** 3 In Stock

-

1

+

A\$1,728⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	A\$1,728.00 each
Need More?	Request Quote

Product Downloads

General	
Macro Zoom Lens	Type:
Physical & Mechanical Properties	
178.13	Length (mm):
63.00	Maximum Diameter (mm):
840.00	Weight (g):

Optical Properties

6:1 Zoom Ratio:

Focal Length Range (mm):

18.6-111

Working Distance (mm): 127 - ∞

Aperture (f/#): f/2.5 - f/16

Lens Wavelength Range:

Sensor	Temperature	Humidity	Light	Sound	Gas	Proximity	Acceleration	Rotation	Position
Temperature	25.0	65.0	100.0	50.0	0.0	0.0	0.0	0.0	0.0
Humidity	25.0	65.0	100.0	50.0	0.0	0.0	0.0	0.0	0.0
Light	25.0	65.0	100.0	50.0	0.0	0.0	0.0	0.0	0.0
Sound	25.0	65.0	100.0	50.0	0.0	0.0	0.0	0.0	0.0
Gas	25.0	65.0	100.0	50.0	0.0	0.0	0.0	0.0	0.0
Proximity	25.0	65.0	100.0	50.0	0.0	0.0	0.0	0.0	0.0
Acceleration	25.0	65.0	100.0	50.0	0.0	0.0	0.0	0.0	0.0
Rotation	25.0	65.0	100.0	50.0	0.0	0.0	0.0	0.0	0.0
Position	25.0	65.0	100.0	50.0	0.0	0.0	0.0	0.0	0.0

Sensor

2/3" **Maximum Sensor Format:**

Threading & Mounting

Threading & Mounting

M58.0 x0.75

C-Mount

Regulatory Compliance

[View](#) Certificate of Conformance:

Product Details

- Large Zoom
- Close Focus Capability
- Broad Field of View Range

Close Focus Zoom Lenses are ideal for multipurpose applications that need both close focus and wide fields of view. The lenses offer variable apertures, to adjust the depth of field. Filter threading allows the use of filters to adjust incoming light levels with ND filters, or increase contrast with color filters on monochrome sensors, and more. Close Focus Zoom Lenses are economical and compact, and these lenses have many features that make them a perfect choice for a variety of uses. These zoom lenses feature 10X magnification and are compatible with C-mounts.

Note: #58-240 Close Focus Zoom Lens can be used for working distances from 127mm to infinity, where its field of view would be 8 - 48mm (horizontal for 2/3" sensors) at minimum working distance.

Technical Information

