

165mm FL, 532nm Edmund Optics® F-Theta Lens



Stock #15-186 3-5 DAYS

⊖ 1 ⊕ **A\$1,467.20**

ADD TO CART

Qty 1-4
A\$1,467.20
Qty 5+
A\$1,320.00
Volume Pricing
Request Quote

Get Product Downloads

Design Wavelength DWL (nm):
532

Focal Length FL (mm):
165.00

Maximum Diameter (mm):
106

Scan Angle (°):
±25.00

Scan Field (mm): 101.8 x 101.8
Mounting Threads: M85 x 1.0
Telecentricity (°): Not Specified
Transmission (%): ≥95
Type: F-Theta Lens
Working Distance (mm): 193.5
Wavelength Range (nm): 532
Range Distance (mm): 228.0
Focus Size Diameter, 1/e² (μm): 13
Input Beam Diameter, 1/e² (mm): 16
Maximum Length (mm): 52.6

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View