

TECHSPEC® 18mm Dia. x 30mm FL, VIS 0° Coated, Achromatic Lens



Stock **#47-705** 3-5 DAYS

[Other Coating Options](#)

- 1 + **A\$156.80**

ADD TO CART

Qty 1-5
A\$156.80
Qty 6+
A\$125.60
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
18.00 +0.0/-0.025

Effective Focal Length EFL (mm):
30.00

Focal Length Tolerance (%) : ±1
Back Focal Length BFL (mm) : 24.97
Focal Length Specification Wavelength (nm) : 587.6
Clear Aperture CA (mm) : 17.00
Centering (arcmin) : <1
Center Thickness CT (mm) : 8.91 ±0.20
Center Thickness CT 1 (mm) : 6.91 ±0.10
Center Thickness CT 2 (mm) : 2.00 ±0.10
Radius R₁ (mm) : 20.73
Radius R₂ (mm) : -14.31
Radius R₃ (mm) : -133.58
Edge Thickness ET (mm) : 6.55
Substrate : ☐ N-BAF10 / N-SF10
Surface Quality : 40-20
f/# : 1.67
Numerical Aperture NA : 0.30
Coating : VIS 0° (425-675nm)
Coating Specification : R _{avg} ≤0.4% @ 425 - 675nm
Power (P-V) @ 632.8nm : 1.5λ
Irregularity (P-V) @ 632.8nm : λ/4
Bevel : Protective bevel as needed
Type : Achromatic Lens
Wavelength Range (nm) : 425 - 675

Regulatory Compliance

RoHS 2015 : Compliant
Reach 219 : Compliant
Certificate of Conformance : View