

170mm, 355nm JENar™ Silverline™ F-Theta Scanning Lens

See More by [Jenoptik](#)



Stock #16-771 3-5 DAYS

-

1

+

A\$10,664.00

ADD TO CART

Qty 1+
A\$10,664.00

Volume Pricing
Request Quote

Get Product Downloads

Focal Length FL (mm):
170.00

Substrate: ☐
[Fused Silica](#) (Corning 7980)

Model Number:
586840

Maximum Diameter (mm):
146 +0/-0.2

Scan Angle (°):
±25

Scan Field (mm): 100 x 100
Mounting Threads: M85 x 1
Telecentricity (°): F-Theta Only: 4.80 With Scanner: 4.80
Type: JENar Silverline F-Theta
Weight (g): 1850
Working Distance (mm): 235.8
Note: Damage Warning: Not recommended for picosecond and femtosecond laser pulses.
Wavelength Range (nm): 355
Protective Window: #17-698 : One Included
Manufacturer: Jenoptik
Damage Threshold, By Design: ☐ 1.0 J/cm ² * (τ/[ns]) ^{0.40} 1.0 MW/cm ²
Scan Field Diameter (mm): 140
X/Y Mirror Angle (°): ±8.9
Range Distance (mm): 315.8
Focus Size Diameter, 1/e² (μm): 11
GDD Specification (fs²): 8490
Input Beam Diameter, 1/e² (mm): 10
Maximum Length (mm): 106.6

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View