

TECHSPEC® 1mm Dia. x 3.0mm FL, MgF₂ Coated, Achromatic Doublet Lens



MgF₂ Coated Achromatic Lenses



Stock #65-566 3-5 DAYS

- 1 +

A\$372.80

ADD TO CART

Qty 1-5

A\$372.80

Qty 6+

A\$298.40

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
1.00 +0.0/-0.025

Effective Focal Length EFL (mm):
3.00

Focal Length Tolerance (%) : ±2
Back Focal Length BFL (mm) : 2.48
Focal Length Specification Wavelength (nm) : 587.6
Clear Aperture CA (mm) : 0.5
Centering (arcmin) : 30-45
Center Thickness CT (mm) : 1.00 ±0.10
Center Thickness CT 1 (mm) : 0.50 ±0.05
Center Thickness CT 2 (mm) : 0.50 ±0.05
Radius R₁ (mm) : 1.75
Radius R₂ (mm) : -1.75
Radius R₃ (mm) : -7.13
Edge Thickness ET (mm) : 0.91
Substrate :  N-PSK53A / N-LASF9
Surface Quality : 20-10
f/# : 3.00
Numerical Aperture NA : 0.17
Coating : MgF ₂ (400-700nm)
Coating Specification : R _{avg} ≤1.75% @400 - 700nm
Power (P-V) @ 632.8nm : 1.5λ
Irregularity (P-V) @ 632.8nm : λ/4
Bevel : Protective bevel as needed
Type : Achromatic Lens
Wavelength Range (nm) : 400 - 700

Regulatory Compliance

RoHS 2015 : Compliant
Reach 224 : Compliant
Certificate of Conformance : View