

[See all 5 Products in Family](#)

2 - 5.5um InAsSb Photovoltaic Multi-Juncton IR Detector, PVMA-1TE-5-1x1-TO39-pSiAR-70



2 - 5.5um InAsSb Photovoltaic Multi-Juncton IR Detector, PVMA-1TE-5-1x1-TO39-pSiAR-70

Stock #90-461 NEW **2 In Stock**

⊖ 1 ⊕ A\$640⁰⁰

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1+ | A\$640.00 each |
| Need More? | Request Quote |

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

General

| | |
|------------------------------|----------------------|
| IR Photovoltaic Detector | Type: |
| PVMA-1TE-5-1x1-TO39-pSiAR-70 | Model Number: |
| TO-39 | Package: |
| Vigo Photonics | Manufacturer: |

Physical & Mechanical Properties

7 **Weight (g):**

1.00 x 1.00 **Active Area (mm):**

Optical Properties

2000 - 5500 **Spectral Response (nm):**

70 **Acceptance Angle (°):**

Environmental & Durability Factors

-20 to +70 **Operating Temperature (°C):**

-20 to +85 **Storage Temperature (°C):**

Regulatory Compliance

Compliant **RoHS 2015:**

View **Certificate of Conformance:**

Compliant **Reach 250:**

Product Details

- Mid and Long-Wave Infrared (MMR/LWIR) Spectral Range
- 1 × 1mm² Active Areas with Acceptance Angles up to 90°
- TO-39 and TO-8 Package Styles with Specialized Anti-Reflection Windows

Vigo Photonics Infrared Detectors deliver high-performance mid and long-wave IR detection with exceptional sensitivity and stability across demanding applications. These HgCdTe and InAsSb detectors are available with a variety of cooling configurations, including single, dual, triple, and quad-stage thermoelectric coolers, to optimize signal-to-noise ratios. Models are offered with active areas of 1 × 1mm² and acceptance angles up to 90°, providing flexibility for system integration. Vigo Photonics Infrared Detectors feature precision packaging options such as TO-39 and TO-8 housings with specialized anti-reflection coatings for maximum throughput. These detectors combine reliability with infrared technology, making them ideal for spectroscopy, gas analysis, and defense applications.