

TECHSPEC[®] 18.0mm Dia. x 36.0mm FL, VIS-EXT Coated Plano-Convex Lens



Stock **#88-706** [CONTACT US](#)
[Other Coating Options](#)

-

1

+

A\$71.20

ADD TO CART

Qty 1-9
A\$71.20
Qty 10+
A\$64.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
18.00 +0.0/-0.025

Effective Focal Length EFL (mm):
36.00 @ 587.6nm

Back Focal Length BFL (mm): 33.65
Coating: VIS-EXT (350-700nm)
Coating Specification: R _{avg} <0.5% @ 350 - 700nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 3.57 ±0.10
Edge Thickness ET (mm): 1.25
Radius R₁ (mm): 18.62
Clear Aperture CA (mm): 17
f/#: 2
Numerical Aperture NA: 0.25
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 350 - 700
Damage Threshold, By Design: ☐ 5 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant