


TECHSPEC® 2" Dia, 12" FL 400-750nm, Spherical Mirror



Stock #72-990 **10 In Stock**

⊖ 1 ⊕ A\$435²⁰

ADD TO CART

Volume Pricing	
Qty 1-5	A\$435.20 each
Qty 6-24	A\$348.80 each
Need More?	Request Quote

Product Downloads

General

Spherical Mirror **Type:**

Physical & Mechanical Properties

50.80 +0.5/-0 **Diameter (mm):**

Ground **Back Surface:**

2.0	Diameter (inches):
+0.02/-0	Diameter Tolerance (inches):
0.50	Edge Thickness ET (inches):
12.70	Edge Thickness ET (mm):
+0.0/-15	Edge Thickness Tolerance (%):
Optical Properties	
Dielectric	Coating Type:
Dielectric Mirror (400-750nm)	Coating:
400 - 750	Wavelength Range (nm):
304.80	Effective Focal Length EFL (mm):
BOROFLOAT®	Substrate: <input type="checkbox"/>
f/6	Aperture (f#):
R _{avg} >98% @400 - 750nm (0 - 45°) R _{avg} >99% @400 - 750nm (0°)	Coating Specification:
12.00	Effective Focal Length EFL (inches):
±2	Focal Length Tolerance (%):
λ/4	Surface Accuracy:
60-40	Surface Quality:
0.5 J/cm ² @ 532nm, 20ns, 20Hz	Damage Threshold, By Design: <input type="checkbox"/>
609.60	Radius of Curvature (mm):




Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Ideal for Multispectral Focusing Applications
- Average Reflectivity >99% Over Broad UV, Visible, and NIR Wavelengths
- Multiple Sizes Available

TECHSPEC® Broadband Dielectric Spherical Mirrors are ideal for light collection in multispectral imaging applications. These mirrors feature greater than 99% reflection, significantly better than metal-coated mirrors, and increase system performance by minimizing energy loss. A BOROFLOAT® substrate provides a good combination of performance and value. TECHSPEC® Broadband Dielectric Spherical Mirrors are available in diameters ranging from 25.4 to 152.4mm for ease of system integration. These mirrors collect and focus light without introducing chromatic aberration.

Technical Information



;