

TECHSPEC® 18mm Dia. x 125mm FL, VIS-NIR Coated, Achromatic Lens



Stock **#49-347** 3-5 DAYS

[Other Coating Options](#)

- 1 + **A\$163.20**

ADD TO CART

Qty 1-5
A\$163.20
Qty 6+
A\$130.40
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
18.00 +0.0/-0.025

Effective Focal Length EFL (mm):
125.00

Focal Length Tolerance (%): ±1
Back Focal Length BFL (mm): 121.95
Focal Length Specification Wavelength (nm): 587.6
Clear Aperture CA (mm): 17.00
Centering (arcmin): <1
Center Thickness CT (mm): 6.50 ±0.20
Center Thickness CT 1 (mm): 4.50 ±0.10
Center Thickness CT 2 (mm): 2.00 ±0.10
Radius R₁ (mm): 76.92
Radius R₂ (mm): -55.48
Radius R₃ (mm): -162.59
Edge Thickness ET (mm): 5.72
Substrate: ☐ N-BK7 / N-SF5
Surface Quality: 40-20
f/#: 6.94
Numerical Aperture NA: 0.07
Coating: VIS-NIR (400-1000nm)
Coating Specification: R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870nm R _{avg} ≤1.25% @ 890 - 1000nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Achromatic Lens
Wavelength Range (nm): 400 - 1000

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View