

[See all 12 Products in Family](#)

## 200µm Aperture Diameter, Chrome on Glass Aperture



Stock #90-739 NEW **3 In Stock**

A\$296.<sup>00</sup>

ADD TO CART

Volume Pricing	
Qty 1+	A\$296.00 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

### Physical & Mechanical Properties

25.4	Outer Diameter (mm):
200 ± 5.0	Fixed Aperture Diameter (µm):
0.06 ± 0.004	Thickness (inches):
1.52	Thickness (mm):
±0.1	Thickness Tolerance (mm):

## Optical Properties

Low Reflective Chrome

Coating:

## Regulatory Compliance

[View](#)

Certificate of Conformance:

## Product Details

- Chrome Coating on Glass Substrate
- Ideal for Precise Beam Control, Modulation, or Optical Alignment
- Pinhole Diameters Ranging from 10 $\mu$ m to 1,000 $\mu$ m

Chrome Coated Glass Optical Apertures are composed of soda lime float glass with low reflective chrome coating for high-contrast performance. These apertures are designed with pinhole diameters ranging from 10 $\mu$ m to 1000 $\mu$ m. The apertures have an overall diameter of 25.4mm (1") and a thickness of 1.52mm, ensuring easy integration with a wide variety of optical mounts. Chrome coating on glass provides a stable and circular aperture diameter immune to bending or creasing. Chrome Coated Glass Optical Apertures are designed to provide high-precision light control, ideal for beam shaping, spatial filtering, and alignment in advanced photonic systems.