

**TECHSPEC® 20.0mm Diameter x -100 FL, NIR I Coated, Plano-Concave Lens**Stock #22-247 **4 In Stock**[Other Coating Options](#)   **A\$79<sup>.60</sup>****ADD TO CART**

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-9        | <b>A\$79.60</b> each          |
| Qty 10-25      | <b>A\$71.60</b> each          |
| Qty 26-49      | <b>A\$63.60</b> each          |
| Need More?     | <a href="#">Request Quote</a> |

## Product Downloads

**SPECIFICATIONS****General**

Type:

## Physical & Mechanical Properties

|                                  |                      |
|----------------------------------|----------------------|
| Diameter (mm):                   | 20.00 +0.0/-0.025    |
| Bevel:                           | Protective as needed |
| Center Thickness CT (mm):        | 3.50                 |
| Center Thickness Tolerance (mm): | ±0.10                |
| Centering (arcmin):              | <1                   |
| Clear Aperture CA (mm):          | 19.00                |
| Edge Thickness ET (mm):          | 4.42                 |

## Optical Properties

|   |  |
|---|--|
| Effective Focal Length EFL (mm):            | -100.00                                    |
| Substrate:                                  | N-BK7                                      |
| f#:   | 4.00                                       |
| Numerical Aperture NA:                      | 0.13                                       |
| Coating:                                    | NIR I (600-1050nm)                         |
| Wavelength Range (nm):                      | 600 - 1050                                 |
| Back Focal Length BFL (mm):                 | -102.88                                    |
| Coating Specification:                      | $R_{avg} \leq 0.5\% @ 600 - 1050\text{nm}$ |
| Focal Length Specification Wavelength (nm): | 587.6                                      |
| Focal Length Tolerance (%):                 | ±1   |
| Radius R <sub>1</sub> (mm):                 | -51.68                                     |
| Surface Quality:                            | 40-20                                      |
| Damage Threshold, By Design:                | 7 J/cm <sup>2</sup> @ 1064nm, 10ns         |
| Power (P-V) @ 632.8nm:                      | 1.5λ                                       |
| Irregularity (P-V) @ 632.8nm:               | N4   |

## Regulatory Compliance


|                             |                      |
|-----------------------------|----------------------|
| RoHS 2015:                  | Compliant            |
| Certificate of Conformance: | <a href="#">View</a> |
| Reach 235:                  | Compliant            |

## PRODUCT DETAILS


- AR Coated to Provide <0.5% Reflectance per Surface for 600 - 1050nm
- Designed for 0° Angle of Incidence
- Various Coating Options: [Uncoated](#), [VIS-EXT](#), [MgF<sub>2</sub>](#), [VIS 0°](#), [VIS-NIR](#), [YAG-BBAR](#), and [NIR II](#)

TECHSPEC® NIR I Coated Plano-Concave (PCV) Lenses are designed to bend parallel input rays to diverge from one another on the output side of the lens causing this lens to have a negative focal length. These lenses can be used for balancing aberrations created by other lenses within a system due to their negative spherical aberration. Plano-Concave (PCV) lenses are commonly used in a variety of applications including image reduction, beam expansion and telescopes. TECHSPEC® NIR I Coated Plano-Concave (PCV) Lenses offer optimal performance in the 600nm to 1050nm range. These lenses are also available [Uncoated](#), [VIS-EXT](#), [MgF<sub>2</sub>](#), [VIS 0°](#), [VIS-NIR](#), [YAG-BBAR](#), or with [NIR II](#) AR coating options.

## TECHNICAL INFORMATION




**NIR I Coating**  
 $R_{avg} \leq 0.5\% @ 600 - 1050\text{nm}$   
 Typ. Energy Density Limit: 7 J/cm<sup>2</sup> @ 1064nm, 10ns



N-BK7


#### Uncoated N-BK7 Typical Transmission



Typical transmission of a 3mm thick, uncoated N-BK7 window across the UV- NIR spectra.

[Click Here to Download Data](#)

#### N-BK7 with MgF<sub>2</sub> Coating Typical Transmission



Typical transmission of a 3mm thick N-BK7 window with MgF<sub>2</sub> (400-700nm) coating at 0° AOI.


The blue shaded region indicates the coating design wavelength range, with the following specification:

$R_{avg} \leq 1.75\% @ 400 - 700\text{nm}$  (N-BK7)

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

#### N-BK7 with VIS-EXT Coating Typical Transmission




Typical transmission of a 3mm thick N-BK7 window with MS-EXT (350-700nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$$R_{avg} \leq 0.5\% @ 350 - 700nm$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)



Typical transmission of a 3mm thick N-BK7 window with MS-NIR (400-1000nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:


$$R_{abs} \leq 0.25\% @ 880nm$$

$$R_{avg} \leq 1.25\% @ 400 - 870nm$$

$$R_{avg} \leq 1.25\% @ 890 - 1000nm$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)




Typical transmission of a 3mm thick N-BK7 window with VIS 0° (425-675nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$$R_{avg} \leq 0.4\% @ 425 - 675nm$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)



Typical transmission of a 3mm thick N-BK7 window with YAG-BBAR (500-1100nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:


$$R_{abs} \leq 0.25\% @ 532nm$$

$$R_{abs} \leq 0.25\% @ 1064nm$$

$$R_{avg} \leq 1.0\% @ 500 - 1100nm$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)




Typical transmission of a 3mm thick N-BK7 window with NIR I (600 - 1050nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:


$$R_{avg} \leq 0.5\% @ 600 - 1050nm$$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)



## N-BK7 with NIR II Coating Typical Transmission



Typical transmission of a 3mm thick N-BK7 window with NIR II (750 - 1550nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$R_{abs} \leq 1.5\% @ 750 - 800\text{nm}$   
 $R_{abs} \leq 1.0\% @ 800 - 1550\text{nm}$   
 $R_{avg} \leq 0.7\% @ 750 - 1550\text{nm}$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

## CUSTOM

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).