

TECHSPEC[®] 18mm Dia. x 50mm FL, VIS-NIR, Inked, Achromatic Lens



Stock **#49-343-INK** 3-5 DAYS
[Other Coating Options](#)

-

1

+

A\$179.20

ADD TO CART

Qty 1-5
A\$179.20
Qty 6+
A\$143.20
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
18.00 ±0.025

Effective Focal Length EFL (mm):
50.00

Focal Length Tolerance (%) : ±1
Back Focal Length BFL (mm) : 45.24
Focal Length Specification Wavelength (nm) : 587.6
Clear Aperture CA (mm) : 17.00
Centering (arcmin) : <1
Center Thickness CT (mm) : 7.30 ±0.20
Center Thickness CT 1 (mm) : 5.00 ±0.10
Center Thickness CT 2 (mm) : 2.30 ±0.10
Radius R₁ (mm) : 27.12
Radius R₂ (mm) : -25.66
Radius R₃ (mm) : -538.70
Edge Thickness ET (mm) : 5.69
Substrate : ☐ N-SSK6 / N-SF10
Surface Quality : 40-20
f/# : 2.78
Numerical Aperture NA : 0.18
Coating : VIS-NIR (400-1000nm)
Coating Specification : R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870nm R _{avg} ≤1.25% @ 890 - 1000nm
Power (P-V) @ 632.8nm : 1.5λ
Irregularity (P-V) @ 632.8nm : λ/4
Bevel : Protective bevel as needed
Type : Achromatic Lens
Wavelength Range (nm) : 400 - 1000

Regulatory Compliance

RoHS : Compliant
Certificate of Conformance : View