


[See all 1 Products in Family](#)

18mm Dia x -46 FL MgF₂ Coated, Achromatic Lens



Stock #30-448 **CLEARANCE** 20+ In Stock

⊖ 1 ⊕ A\$20⁷²

ADD TO CART

Volume Pricing

Qty 1+ A\$20.72 each

Need More? [Request Quote](#)

Product Downloads

General

Achromatic Lens **Type:**

Physical & Mechanical Properties

18.00 **Diameter (mm):**

Optical Properties

-46.00 **Effective Focal Length EFL (mm):**

f#:

2.56

0.20

Numerical Aperture NA:

MgF₂ (400-700nm)

Coating:

R_{avg} ≤ 1.75% @ 400 - 700nm

Coating Specification:

400 - 700

Wavelength Range (nm):

Regulatory Compliance

[View](#)

Certificate of Conformance:

Product Details

- Correct for Color and On-Axis Aberrations
- MgF₂ Coated for Low Reflection
- Ideal for use as Barlow Lenses

Consisting of two optical elements cemented together, negative achromats are corrected for color and on-axis aberrations. Used predominantly as Barlow lenses to extend focal lengths, they are often combined with positive achromatic mirror systems and imaging lenses.

Coating Curves

;