

# 1.9mm FL, No IR-Cut Filter, f/2, Micro Video Lens



Stock #64-106 3-5 DAYS

- 1 + **A\$92.80**

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-49                      |
| A\$92.80                      |
| Qty 50+                       |
| A\$75.20                      |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

## Get Product Downloads

Length (mm):  
15.20

Filter Thread:  
M12 x 0.50

Maximum Diameter (mm):  
17.0

Maximum Image Circle (mm):  
4.50

|                                                             |
|-------------------------------------------------------------|
| <b>Horizontal Field of View @ Max Sensor Format:</b><br>118 |
| <b>Note:</b><br>Standard                                    |
| <b>Type:</b><br>M12 Imaging Lens                            |
| <b>Focal Length FL (mm):</b><br>1.90                        |
| <b>Maximum Sensor Format:</b><br>1/4"                       |
| <b>Working Distance (mm):</b><br>400 - ∞                    |
| <b>Mount:</b><br>M12 x0.5 (S-Mbunt)                         |
| <b>Aperture (f/#):</b><br>f/2                               |
| <b>IR Cut Filter:</b><br>No                                 |
| <b>Lens Wavelength Range:</b><br>VIS                        |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>Reach 205:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |