

[See all 5 Products in Family](#)

Photometrics Moment USB 3.2 Camera, 1T-01-MOMENT-MONO



Stock **#90-393** NEW **1 In Stock**

-

1

+

A\$9,120⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	A\$9,120.00 each
Need More?	Request Quote

Product Downloads

Monochrome	Spectrum:
General	
Monochrome Camera	Type:
1T-01-MOMENT-MONO	Model Number:
Teledyne Photometrics	Manufacturer:

Moment	Camera Series:
	Note:
Includes: USB Interface Card USB cable (2) single-line MMCX trigger cables USB memory device containing PVCAM library and drivers Quick Installation Guide	

Physical & Mechanical Properties

40 x 42 x 50	Dimensions (mm):
96	Weight (g):
Full	Housing:

Optical Properties

300 - 1100	Wavelength Range (nm):
------------	------------------------

Sensor

1.1"	Sensor Format:
7.00	Resolution (Megapixels):
51.00	Frame Rate (fps):
3,200 x 2,200	Pixels (H x V):
14.4 x 9.9	Sensing Area, H x V (mm):
Sony-Based	Imaging Sensor:
Progressive Scan CMOS	Type of Sensor:
Global	Shutter Type:
12 bit	Pixel Depth:
12µs- 1s	Exposure Time:
72	Dynamic Range (dB):

Hardware & Interface Connectivity

USB 3.2 Gen 2	Connector:
Power over USB	Power Supply:
1 configurable input, 1 configurable outputs	GPIOs:
Hardware Trigger (GPIO) or Software Trigger	Synchronization:
Back Panel	Interface Port Orientation:
BNC	GPIO Connector Type:

Threading & Mounting

C-Mount	Mount:
(1) M3 x 0.5 thread per side	Mounting Threads:

Environmental & Durability Factors

0 to 30	Operating Temperature (°C):
−20 to 60	Storage Temperature (°C):

Regulatory Compliance

Exempt	RoHS 2015:
	Certificate of Conformance:

View	
Contains SVHC(s)	Reach 247:

Product Details

- Ultra-Compact CMOS
- Low Noise, High Speed Imaging
- True Global Shutter
- Scientific Cameras for High Sensitivity Microscopy Applications



Teledyne Photometrics Mment USB 3.2 Cameras measure just 50 × 40 × 42 mm and operate with a single high-speed USB 3.2 Gen 2 cable. This allows seamless integration into space-limited microscope systems and complex multi-device workflows. These cameras feature a low-read-noise CMOS sensor coupled with a true global shutter, achieving high-speed imaging at up to 50 fps with 12-bit depth. Teledyne Photometrics Moment USB 3.2 cameras are ideal for demanding applications such as live-cell imaging, light-sheet microscopy, and super-resolution microscopy. These cameras include Teledyne's proprietary-designed software platforms, Beacon and PVCAM, for optimizing camera performance and ease of system integration.